



Cut



Medium Duty

## Durable increased visibility work gloves, designed to protect workers in low-light conditions

- **Specialized protection:** ActivArm<sup>®</sup> 97-013 industrial gloves possess high-visibility features on the palm and back of the hand, with a retro-reflective logo, to ensure wearer safety in dark/low-light conditions
- **Optimized comfort:** With a 13-gauge fiberglass and polyester liner, ActivArm<sup>®</sup> 97-013 safety work gloves keep hands comfortable and sweat-free throughout the day
- **Advanced ergonomics:** These hand protection gloves offer a naturally curved, relaxed fit, for reduced hand fatigue and increased dexterity
- **Improved cut resistance:** They are also designed with INTERCEPT™ Cut Resistance Technology, for better laceration defenses
- **Added grip:** ActivArm<sup>®</sup> 97-013 medium-duty gloves boast excellent grip in both wet and dry working environments



### Industries

- Mining
- Oil and gas

### Applications

- Signalling/Positioning
- Operating of heavy machinery
- Loading and hauling
- Hydraulic repair
- Shipping and loading of product
- Vehicle Maintenance
- General pumping work
- Preparation of site - set-up and disassembly of tool string
- Set-up of pressure manifold and tubing injector head
- Handling of tools
- Valve - line maintenance and repair
- Handling jagged metal
- Equipment maintenance Scaffolding Pipe handling and insulation Plumbing and sand blasting
- Heavy machine operation

# ACTIVARMR®

PERSONAL PROTECTIVE GEAR

## 97-013

Medium duty increased visibility glove

### Key Features

- **Extra visibility back and palm:** Protecting hands in dark environments
- **13-gauge fiberglass and polyester liner:** Sweat-proof all-day comfort
- **Ergonomic design:** Naturally curved fit, for reduced hand fatigue

### Performance Standards & Regulatory Compliance



ANSI/ISEA 105-2024



4X32B

### Technologies



**INTERCEPT™**  
Cut Resistance Technology

### Specifications

BRAND   STYLE	DESCRIPTION	Gauge	SIZE	LENGTH	COATING COLOR	PACKAGE
ActivArm® 97-013	<b>Finishing:</b> Palm Coated <b>Coating Material:</b> Water-Based polyurethane and nitrile <b>Liner Material:</b> Fiber glass, Polyester <b>Cuff Style:</b> Knitwrist	13	7, 8, 9, 10, 11	230-270 mm/ 9.05-10.63 inches	Orange	12 pairs/bag, 6 bags/carton

For additional information visit us at [www.ansell.com](http://www.ansell.com), or call us at

#### Europe, Middle East & Africa Region

Ansell Healthcare Europe NV  
Riverside Business Park  
Blvd International, 55  
1070 Brussels, Belgium  
T: +32 (0) 2 528 74 00  
F: +32 (0) 2 528 74 01

#### North America Region

Ansell Healthcare Products LLC  
111 Wood Avenue South,  
Suite 900  
Iselin, NJ 08830, USA  
T: +1 800 800 0444  
F: +1 800 800 0445

#### Australia

Ansell Limited  
Level 3,678 Victoria Street,  
Richmond, Vic, 3121  
Australia  
T: +61 1800 337 041  
F: +61 1800 803 578

#### Asia Pacific Region

Ansell Global Trading Center  
(Malaysia) Sdn Bhd  
Prima 6, Prima Avenue  
Block 3512, Jaijan Teknokrat 6  
T: +603 8310 6688  
F: +603 8310 6699

#### Latin America & Caribbean Region

Ansell Commercial Mexico S.A. de C.V.  
Blvd. Bernardo Quintana No. 7001-C,  
Q7001 Torre II,  
Suites 1304, 1305 y 1306,  
Col. Centro Sur, c.p. 76079  
Queretaro, Qro. Mexico  
T: +52 442 248 1544 / 248 3133

#### Canada

Ansell Canada  
105 Lauder  
Cowansville, QC J2K 2K8  
Canada  
T: +1 800 363 8340  
F: +1 800 267 3551

Ansell, ® and ™ are trademarks owned by Ansell Limited or one of its affiliates. US Patented and US and non-US Patents Pending: [www.ansell.com/patentmarking](http://www.ansell.com/patentmarking) © 2024 Ansell Limited. All Rights Reserved.

Neither this document nor any other statement made herein by or on behalf of Ansell should be construed as a warranty of merchantability or that any Ansell product is fit for a particular purpose. Ansell assumes no responsibility for the suitability or adequacy of an end user's selection of gloves for a specific application.

