

Dual-layer, chemical-resistant EMS gloves, offering wearers advanced barrier protection

- **Reinforced defenses:** MICROFLEX[®] LifeStar EC[™] 93-868 chemical-resistant EMS gloves' dual-layer, dual-color design offers users reinforced barrier protection and chemical resistance
- **Specialized protection:** These nitrile gloves' layered design also satisfies EN 374 Type B standards for chemical splash protection
- **Sustained grip:** Textured fingertips and a non-stick/non-foaming composition help medical users and healthcare professionals maintain a strong grip in dry and wet conditions
- **Extended protection:** These medical gloves' boast an extended cuff over the wrist and lower forearm, protecting workers on the job
- **Low AQL:** These medical exam gloves' low 0.65 AQL reinforces their barrier integrity



Industries

- Chemical
- Life Sciences
- Food Processing
- Healthcare

Recommended For

- Administering drugs
- Inspection, selecting, checking parts
- Sample taking and processing
- Transferring liquids and solids

TECHNICAL DATA SHEET

	Product Information
External Glove Surface	Textured Fingers
Audit Standards	ISO 13485, ISO 9001
Product Certification	Medical Device Regulation (EU) 2017/745 Class I, Personal Protective Equipment Regulation (EU) 2016/425 Category III risks , FDA21 CFR 177-2600-US Food Contact Approved , Category III, ASTM D6319 , EN ISO 21420:2020, NFPA 1999:2013,EN 455 1-4,EN 16523-1
Packaging Overview	100 gloves per dispenser 10 dispensers per case 1000 gloves per case XXXL: 90 gloves per dispenser
Storage Instructions	Keep out of direct sunlight; store in a cool and dry place. Keep away from sources of ozone or ignition.
Country Of Origin	Malaysia
Product Segmentation	High Risk
Antistatic	Yes EN1149


PHYSICAL PROPERTIES

	Typical Values		Testing Method
Length (mm/inches)	≥ 280 / 11.0		ASTM D3767,EN 420
Freedom from Holes (Inspection level I)	0.65 AQL		ASTM D5151,EN 374-2
Palm Thickness (mm/mils)	0.14 / 5.5		ASTM D3767,EN 420
Finger Thickness (mm/mils)	0.21 / 8.3		ASTM D3767,EN 420
	BEFORE AGING	AFTER AGING	
Ultimate Tensile Strength (MPa)	≥ 25	≥ 25	ASTM D412 & D573
Elongation at Break (%)	≥ 700	≥ 650	ASTM D412
Force at break (N)	≥ 9	≥ 10	EN 455-2

ORDERING INFORMATION

Size	S (6.5 - 7)	M (7.5 - 8)	L (8.5 - 9)	XL (9.5 - 10)	XXL (10.5 - 11)
Product Code	93868070	93868080	93868090	93868100	93868110

Performance Standards and Regulatory Compliance



For additional information visit us at www.ansell.com, or call us at

Europe, Middle East & Africa Region Ansell Healthcare Europe NV T: +32 (0) 2 528 74 00 F: +32 (0) 2 528 74 01 Asia Pacific Region MY: +603 8310 6688 apac.medical@ansell.com CN: +86 21 38275000 infochina@ansell.com JP: +813 5549 8151 info.medical.jp@ansell.com	North America Region Ansell Healthcare Products LLC T: +1 800 800 0444 F: +1 800 800 0445 Latin America & Caribbean Region BR: +55 (11) 3356-3100 latam.medical@ansell.com MX: +52 442 296 2050 latam.medical@ansell.com CO: +57 1 288 3247 latam.medical@ansell.com	Australia Ansell Limited T: +61 1800 337 041 F: +61 1800 803 578 Russia Ansell PYC Ten. +7 495 258 13 16
---	--	--

Ansell, ® and ™ are trademarks owned by Ansell Limited or one of its affiliates. US Patented and US and non-US Patents Pending: www.ansell.com/patentmarking © 2024 Ansell Limited. All Rights Reserved.

Neither this document nor any other statement made herein by or on behalf of Ansell should be construed as a warranty of merchantability or that any Ansell product is fit for a particular purpose. Ansell assumes no responsibility for the suitability or adequacy of an end user's selection of gloves for a specific application.

