

Ultralight, comfortable neoprene exam gloves, recommended for exceptional wet grip

- **Elevated comfort:** Soft neoprene exam gloves featuring ERGOFORM™ Ergonomic Design Technology for extra comfort and support of musculoskeletal health
- **Enhanced grip:** Certified by US Ergonomics for enhanced wet grip capabilities*
- **Heightened tactile sensitivity:** Their thin, ultra-lightweight design offers enhanced tactile sensitivity, for more precise handling of tools and instruments
- **Reduced waste:** Packed 200 per box to reduce packaging waste



*this product has been certified by United States Ergonomics for exceptional wet grip performance in a variety of wet grip test conditions — these included gripping tests involving soap solutions, artificial saliva, artificial blood

Industries

- Healthcare
- Dental
- Veterinary

Recommended For

- Enhanced grip in wet environments
- Environmentally friendly facilities
- Extra comfort during long, sustained procedures
- General dentistry
- Protection from Type I latex allergy in HCW's or patients
- Standard patient examinations

TECHNICAL DATA SHEET

| Product Information | |
|------------------------|--|
| External Glove Surface | Textured Fingers |
| Audit Standards | ISO 13485, ISO 9001 |
| Packaging Overview | Case/Carton=2000 gloves/10 Dispensers; Dispenser=200 gloves (XS-L) |
| | Case/Carton=1800 gloves/10 Dispensers; Dispenser=180 gloves (XL) |
| Storage Instructions | Keep out of direct sunlight; store in a cool and dry place. Keep away from sources of ozone or ignition. |
| Country Of Origin | Indonesia |
| Product Segmentation | High Touch |
| Antistatic | Not Tested |

PHYSICAL PROPERTIES

| | Typical Values | | Testing Method |
|---|---------------------|--------------------|-----------------------|
| Length (mm/inches) | 240 / 9.5 | | ASTM D3767,ASTM D6977 |
| Freedom from Holes (Inspection level I) | 1.5 AQL | | ASTM D5151 |
| Palm Thickness (mm/mils) | 0.07 / 2.8 | | ASTM D3767,ASTM D6977 |
| Finger Thickness (mm/mils) | 0.09 / 3.5 | | ASTM D3767,ASTM D6977 |
| | BEFORE AGING | AFTER AGING | |
| Ultimate Tensile Strength (MPa) | ≥ 14 | ≥ 14 | ASTM D412 & D573 |
| Elongation at Break (%) | ≥ 500 | ≥ 400 | ASTM D412 & D573 |

ORDERING INFORMATION

| Size | XS (5.5 - 6) | S (6.5 - 7) | M (7.5 - 8) | L (8.5 - 9) | XL (9.5 - 10) |
|--------------|--------------|-------------|-------------|-------------|---------------|
| Product Code | 73737060 | 73737070 | 73737080 | 73737090 | 73737100 |

Performance Standards and Regulatory Compliance



For additional information visit us at www.ansell.com, or call us at

Europe, Middle East & Africa Region
 Ansell Healthcare Europe NV
 T: +32 (0) 2 528 74 00
 F: +32 (0) 2 528 74 01

Asia Pacific Region
 MY +603 8310 6688
 apac.medical@ansell.com
 CN: +86 21 38275000
 infochina@ansell.com
 JP: +813 5549 8151
 info.medical.jp@ansell.com

North America Region
 Ansell Healthcare Products LLC
 T: +1 800 800 0444
 F: +1 800 800 0445

Latin America & Caribbean Region
 BR +55 (11) 3356-3100
 latam.medical@ansell.com
 MX: +52 442 296 2050
 latam.medical@ansell.com
 CO: +57 1 288 3247
 latam.medical@ansell.com

Australia
 Ansell Limited
 T: +61 1800 337 041
 F: +61 1800 803 578

Russia
 Ansell PYC
 Ten. +7 495 258 13 16

Technology



Ansell, ® and ™ are trademarks owned by Ansell Limited or one of its affiliates. US Patented and US and non-US Patents Pending; www.ansell.com/patentmarking © 2024 Ansell Limited. All Rights Reserved.

Neither this document nor any other statement made herein by or on behalf of Ansell should be construed as a warranty of merchantability or that any Ansell product is fit for a particular purpose. Ansell assumes no responsibility for the suitability or adequacy of an end user's selection of gloves for a specific application.

