

## Ergonomically designed to reduce hand fatigue

- **Reduced allergy risk:** MICROFLEX<sup>®</sup> 93-733 gloves are manufactured without accelerators for low dermatitis potential. These gloves prevent instances of Type I latex allergies and Type IV chemical allergic reactions
- **Extra durability:** stronger formulation to protect against rips and tears while keeping the same tactile sensitivity
- **Enhanced comfort:** softer formulation for a lightweight, softer skin feel
- **ERGOFORM™ Technology:** MICROFLEX<sup>®</sup> XCEED<sup>®</sup> 93-733 gloves are designed with proprietary ergonomic design technology to support musculoskeletal health and increase worker productivity
- **Reduced waste:** Gloves are smartly packaged, with 250 gloves per box and easy, single glove dispensing to reduce waste
- **Strong barrier integrity:** With a low 0.65 AQL, these gloves offer advanced barrier integrity



### Industries

- Automotive Aftermarket
- Food Processing
- Life Sciences

### Recommended For

- General Purpose Auto Aftermarket
- Plant disinfection and sanitization
- All food processing, applications that have food contact
- Assembly of parts
- Sample taking and processing
- Raw material sample collection
- Enhanced tactile sensitivity and dexterity, especially for delicate procedures
- Protection from Type IV chemical allergies in HCW's or patients

# TECHNICAL DATA SHEET

Product Information	
External Glove Surface	Textured Fingers
Audit Standards	ISO 13485, ISO 9001
Product Certification	Medical Device Regulation (EU) 2017/745 Class I, Personal Protective Equipment Regulation (EU) 2016/425 Category III risks
Packaging Overview	250 gloves per dispenser 10 dispensers per case 2500 gloves per case
Storage Instructions	Keep out of direct sunlight; store in a cool and dry place. Keep away from sources of ozone or ignition.
Country Of Origin	Malaysia
Product Segmentation	High Touch
Antistatic	No

## PHYSICAL PROPERTIES

	Typical Values		Testing Method
Length (mm/inches)	240 / 9.5		ASTM D3767, EN 420
Freedom from Holes (Inspection level I)	0.65 AQL		ASTM D5151, EN 374-2
Palm Thickness (mm/mils)	0.07 / 2.8		ASTM D3767, EN 420
Finger Thickness (mm/mils)	0.11 / 4.3		ASTM D3767, EN 420
	<b>BEFORE AGING</b>	<b>AFTER AGING</b>	
Ultimate Tensile Strength (MPa)	22	14	
Elongation at Break (%)	≥ 500	≥ 400	
Force at break (N)	≥ 6	≥ 6	

## ORDERING INFORMATION

Size	XS (5.5 - 6)	S (6.5 - 7)	M (7.5 - 8)	L (8.5 - 9)	XL (9.5 - 10)
Product Code	93733060	93733070	93733080	93733090	93733100

## Performance Standards and Regulatory Compliance



For additional information visit us at [www.ansell.com](http://www.ansell.com), or call us at

**Europe, Middle East & Africa Region**  
Ansell Healthcare Europe NV  
T: +32 (0) 2 528 74 00  
F: +32 (0) 2 528 74 01

**Asia Pacific Region**  
MY +603 8310 6688  
apac.medical@ansell.com  
CN: +86 21 38275000  
infochina@ansell.com  
JP: +813 5549 8151  
info.medical.jp@ansell.com

**North America Region**  
Ansell Healthcare Products LLC  
T: +1 800 800 0444  
F: +1 800 800 0445

**Latin America & Caribbean Region**  
BR +55 (11) 3356-3100  
latam.medical@ansell.com  
MX +52 442 296 2050  
latam.medical@ansell.com  
CO: +57 1 288 3247  
latam.medical@ansell.com

**Australia**  
Ansell Limited  
T: +61 1800 337 041  
F: +61 1800 803 578

**Russia**  
Ansell PYC  
Ten. +7 495 258 13 16

Technology



Ansell<sup>®</sup> and <sup>™</sup> are trademarks owned by Ansell Limited or one of its affiliates. US Patented and US and non-US Patents Pending: [www.ansell.com/patentmarking](http://www.ansell.com/patentmarking) © 2024 Ansell Limited. All Rights Reserved.

Neither this document nor any other statement made herein by or on behalf of Ansell should be construed as a warranty of merchantability or that any Ansell product is fit for a particular purpose. Ansell assumes no responsibility for the suitability or adequacy of an end user's selection of gloves for a specific application.

