

Long-cuffed disposable gloves, delivering superior chemical splash protection and comfort

- **World leader:** Extended-cuff version of TouchNTuff® 92-600, the world's leading disposable gloves for chemical splash protection
- **Superior, extended cuff protection:** Made with TNT™ Chemical Splash Resistance Technology, these gloves guard hands, wrists and forearms against harmful chemical splashes
- **Elevated comfort:** Super soft nitrile provides a comfortable feel during extended wear
- **Robust durability:** Proprietary formulation is extra-strong to prevent tearing during heavy-duty work
- **Prevents surface defects:** Silicone-free, they prevent contaminant transfer that causes flaws in paints, coatings and finishes



Industries

- Life Sciences
- Food Processing
- Automotive
- Machinery and Equipment
- Chemical

Recommended For

- Sample taking and processing
- Laboratory analysis
- Transferring liquids and solids
- Meat, Fish and Food Processing
- Industrial Production
- Maintenance
- Chemical Handling

TECHNICAL DATA SHEET

| Product Information | |
|------------------------|--|
| External Glove Surface | Textured Fingers |
| Audit Standards | ISO 9001 |
| Packaging Overview | 100 gloves per dispenser 10 dispensers per case 1000 gloves per case |
| Storage Instructions | Keep out of direct sunlight; store in a cool and dry place. Keep away from sources of ozone or ignition. |
| Country Of Origin | Thailand |
| Product Segmentation | High Risk |
| Antistatic | Yes EN1149 |
| Silicone Free | Yes |

PHYSICAL PROPERTIES

| | Typical Values | | Testing Method |
|---|---------------------|--------------------|---------------------|
| Length (mm/inches) | 300 / 12 | | ASTM D3767,EN 420 |
| Freedom from Holes (Inspection level I) | 1.5 AQL | | ASTM D5151,EN 455-1 |
| Palm Thickness (mm/mils) | 0.12 / 4.7 | | ASTM D3767,EN 420 |
| Finger Thickness (mm/mils) | 0.16 / 6.3 | | ASTM D3767,EN 420 |
| | BEFORE AGING | AFTER AGING | |
| Ultimate Tensile Strength (MPa) | ≥ 14 | ≥ 14 | ASTM D412 & D573 |
| Elongation at Break (%) | ≥ 500 | ≥ 400 | ASTM D412 |
| Force at break (N) | ≥ 6 | ≥ 6 | EN 455-2 |

ORDERING INFORMATION

| Size | S (6.5 - 7) | M (7.5 - 8) | L (8.5 - 9) | XL (9.5 - 10) |
|--------------|-------------|-------------|-------------|---------------|
| Product Code | 92605070 | 92605080 | 92605090 | 92605100 |

Performance Standards and Regulatory Compliance



For additional information visit us at www.ansell.com, or call us at

Europe, Middle East & Africa Region

Ansell Healthcare Europe NV
T: +32 (0) 2 528 74 00
F: +32 (0) 2 528 74 01

Asia Pacific Region

MY +603 8310 6688
apac.medical@ansell.com
CN: +86 21 38275000
infochina@ansell.com
JP: +813 5549 8151
info.medical.jp@ansell.com

North America Region

Ansell Healthcare Products LLC
T: +1 800 800 0444
F: +1 800 800 0445

Latin America & Caribbean Region

BR +55 (11) 3356-3100
latam.medical@ansell.com
MX: +52 442 296 2050
latam.medical@ansell.com
CO: +57 1 288 3247
latam.medical@ansell.com

Australia

Ansell Limited
T: +61 1800 337 041
F: +61 1800 803 578

Russia

Ansell PYC
Ten. +7 495 258 13 16

Technology



Ansell, ® and ™ are trademarks owned by Ansell Limited or one of its affiliates. US Patented and US and non-US Patents Pending; www.ansell.com/patentmarking © 2024 Ansell Limited. All Rights Reserved.

Neither this document nor any other statement made herein by or on behalf of Ansell should be construed as a warranty of merchantability or that any Ansell product is fit for a particular purpose. Ansell assumes no responsibility for the suitability or adequacy of an end user's selection of gloves for a specific application.

