

Previously known as: Powerflex®80-658



Cut



Heat



Heavy Duty

High-performance protective gloves, combining cut and heat resistance with excellent grip

- **Advanced defenses:** ActivArm® 80-658 safety gloves' steel, fiberglass and aramid liner affords EN ISO E cut resistance, as well as EN 407 level 2 heat contact resistance, for superior hand protection when handling sharp and warm components
- **Specialized protection:** With their latex coating and raised crinkled finish, these sturdy heavy-duty gloves reduce slippage and muscle tension, protecting hands while ensuring strong grip performance
- **Enhanced features:** For added forearm and wrist protection, ActivArm® 80-658 industrial gloves feature an extra-long, three quarter-dipped, liquid-repellent cuff, shielding the skin from potentially hazardous liquid solutions
- **Added convenience:** These heather green-colored gloves mask dirt, while remaining washable and available in varying sizes



Industries

- Construction
- Glass manufacturing
- Metal fabrication
- Recycling and Waste Disposal

Applications

- Heavy duty handling: where sensitivity is also required
- Handling jagged metal
- Handling of glass sheets, sharpedged objects
- Handling of metal sheets, cutting of dry, painted or galvanised pieces

Previously known as: Powerflex®80-658

Key Features

- **Three-layer construction:** Added cut, splinter and burn resistance
- **Latex coating with crinkled finish:** Firm dry and wet grip
- **Extra-long cuff:** For work gloves offering forearm and wrist protection

Vulcanization Chemical Accelerators

- Natural rubber proteins (in the coating and in the elastic cuff)
- Zinc Diethyldithiocarbamate

Only a very small number of users may be sensitive to this ingredient(s) and hence may develop irritant and/or allergic contact reactions.

Performance Standards & Regulatory Compliance



Specifications

| BRAND STYLE | DESCRIPTION | Gauge | SIZE | LENGTH | COATING COLOR | PACKAGE |
|------------------|--|-------|----------------|-------------------------------|---------------|-----------------------------|
| ActivArm® 80-658 | Finishing: Dipped Coating Material: Natural Latex Rubber Liner Material: Stainless steel, Nylon, Fiber glass, Cotton, Aramid Cuff Style: Extra Long | 7 | 6, 7, 8, 9, 10 | 250-300 mm; 9.84-11.81 inches | Blue | 12 pairs/bag, 6 bags/carton |

For additional information visit us at www.ansell.com, or call us at

Europe, Middle East & Africa Region

Ansell Healthcare Europe NV
 Riverside Business Park
 Blvd International, 55
 1070 Brussels, Belgium
 T: +32 (0) 2 528 74 00
 F: +32 (0) 2 528 74 01

North America Region

Ansell Healthcare Products LLC
 111 Wood Avenue South,
 Suite 900
 Iselin, NJ 08830, USA
 T: +1 800 800 0444
 F: +1 800 800 0445

Australia

Ansell Limited
 Level 3,678 Victoria Street,
 Richmond, Vic, 3121
 Australia
 T: +61 1800 337 041
 F: +61 1800 803 578

Asia Pacific Region

Ansell Global Trading Center
 (Malaysia) Sdn Bhd
 Prima 6, Prima Avenue
 Block 3512, Jaijan Teknokrat 6
 T: +603 8310 6688
 F: +603 8310 6699

Latin America & Caribbean Region

Ansell Commercial Mexico S.A. de C.V.
 Blvd. Bernardo Quintana No. 7001-C,
 Q7001 Torre II,
 Suites 1304, 1305 y 1306,
 Col. Centro Sur, c.p. 76079
 Queretaro, Qro. Mexico
 T: +52 442 248 1544 / 248 3133

Canada

Ansell Canada
 105 Lauder
 Cowansville, QC J2K 2K8
 Canada
 T: +1 800 363 8340
 F: +1 800 267 3551