

## EPDM RABS/isolator gloves, made with premium FDA-approved material, for fewer glove changes

Port size: 254mm/10"  
Thickness: 0.4mm/16 mil

- **Optimized durability:** The AlphaTec® EPDM Isolator Glove 85-502 is designed for repeated autoclave sterilization (up to 50 times), which means fewer replacements
- **Assured protection:** These RABS gloves are EN ISO 374-compliant, resisting hydrogen peroxide and common disinfecting chemicals
- **Increased eco-friendliness:** They are halogen-free, making them suitable for disposal by incineration
- **Food handling compliance:** They comply with FDA Food Contact regulation (FDA Positive List) 21 CFR 177 for Indirect Food Additives



### KEY FEATURES & BENEFITS

- **EPDM material:** Ideal for repeated autoclave sterilization
- **Chemical resistance:** Hydrogen peroxide/common disinfecting chemicals
- **FDA food handling compliance:** For safe, assured food handling

### TECHNICAL DATA SHEET

|                                     |                                                                                                                                 |
|-------------------------------------|---------------------------------------------------------------------------------------------------------------------------------|
| Product Reference                   | 85-502                                                                                                                          |
| Material                            | Ethylene propylene diene rubber_EPDM                                                                                            |
| Color                               | Black                                                                                                                           |
| Shape                               | Ambidextrous                                                                                                                    |
| External Glove Surface              | Smooth                                                                                                                          |
| Cuff Style                          | Beaded                                                                                                                          |
| Storage Instructions                | Store in a dry and dark environment, temperature of 5°C to 22°C. Retain in original packaging when not in use.                  |
| Available Sizes                     | 11, 9.5                                                                                                                         |
| Temperature Range                   | From -20°C to 130°C                                                                                                             |
| Cleanroom Class                     | Non-Critical Environment                                                                                                        |
| Shelf Life                          | Three (3) years from date of manufacture.                                                                                       |
| Standards                           | CE 0493, EN 388:2016, EN ISO 21420:2020, EN ISO 374-1:2016 Type B, EN ISO 374-5:2016, EN 420:2003 + A1:2009, Category III, UKCA |
| Vulcanization Chemical Accelerators | <ul style="list-style-type: none"><li>• Diphenyl guanidine</li><li>• Tetramethylthiuram disulfide</li></ul>                     |

### PHYSICAL PROPERTIES

|                                              | Typical Values   | Testing Method |
|----------------------------------------------|------------------|----------------|
| Typical Length (mm/in)                       | 800mm/32in       | EN ISO 21420   |
| Port Size                                    | 10"              |                |
|                                              |                  |                |
| Target Single Wall Palm Thickness (mm/mil)   | 0.40 mm / 16 mil | EN 455-2       |
| Target Single Wall Finger Thickness (mm/mil) | 0.40 mm / 16 mil | EN 455-2       |
| Target Single Wall Cuff Thickness (mm/mil)   | 0.40 mm /16 mil  | EN 455-2       |

### PROTECTION AGAINST MECHANICAL RISKS, EN 388:2016+A1:2018

| Risk                 | Performance level |
|----------------------|-------------------|
| Abrasion Resistance  | Level 2           |
| Blade Cut Resistance | Level 1           |
| Tear Resistance      | Level 1           |
| Puncture Resistance  | Level 1           |

### ORDERING INFORMATION

|        | PORT SIZE   | 10"/254mm | 10"/254mm |
|--------|-------------|-----------|-----------|
|        | SIZE        | 9.5       | 11        |
| 85-502 | REORDER NO. | 85502095  | 85502110  |

For additional information visit us at [www.ansell.com](http://www.ansell.com), or call us at

#### Europe, Middle East & Africa Region

Ansell Healthcare Europe NV  
T: +32 (0) 2 528 74 00  
F: +32 (0) 2 528 74 01

#### Asia Pacific Region

Ansell Global Trading Center  
T: +603 8310 6688  
F: +603 8310 6699

#### North America Region

Ansell Healthcare Products LLC  
US T: +1 800 800 0444  
US F: +1 800 800 0445  
CA T: +1-800-363-8340

#### Latin America & Caribbean Region

Ansell Commercial Mexico S.A. de C.V.  
T: +52 442 248 1544 / 248 3133

#### Australia

Ansell Limited  
T: +61 1800 337 041  
F: +61 1800 803 578

#### UK

Ansell Nitritex  
T: +44 1638 663338  
F: +44 1638 668890

### Performance Standards and Regulatory Compliance



Ansell, ® and ™ are trademarks owned by Ansell Limited or one of its affiliates. US Patented and US and non-US Patents Pending: [www.ansell.com/patentmarking](http://www.ansell.com/patentmarking) © 2024 Ansell Limited. All Rights Reserved.

Neither this document nor any other statement made herein by or on behalf of Ansell should be construed as a warranty of merchantability or that any Ansell product is fit for a particular purpose. Ansell assumes no responsibility for the suitability or adequacy of an end user's selection of gloves for a specific application.