

HyFlex®

ADVANCED MECHANICAL PROTECTION

11-735

Tough and durable cut protection with a breathable, soft liner



Cut

Abrasion Protection



Medium Duty

Durable gloves meet ANSI/ISEA 105-2024 CUT A4 and EN ISO C standards, providing extended glove life.

- The HyFlex® 11-735's liner is enriched with Lycra® content, and features patented INTERCEPT™ Cut Resistance Technology that meet ANSI/ISEA 105-2024 CUT A4 and EN ISO C standards
- Superior durability: Their palm-dipped PU coating ensures robust PPE gloves with long-lasting resilience, achieving EN ABRASION LEVEL 4 and ANSI/ISEA 105-2024 ABRASION LEVEL 6.
- Lightened comfort: These HyFlex® gloves' 10G lightweight plaited liner ensures a versatile blend of comfort, flexibility and protection
- Enhanced grip: The same polyurethane coating enhances these HyFlex gloves' grip and performance in dry or slightly oily conditions
- Simplified packaging: These PU-coated gloves also come in vend pack form, for convenient access in times of need



Industries

- Automotive
- Machinery and Equipment
- Metal fabrication
- Chemical
- Automotive Aftermarket

Applications

- Metalworking & assembly operations
- Assembly & inspection of components
- Assembly and disassembly of equipment
- Seizing structural parts
- Mounting and dismantling
- Fastening components, parts
- Loading and unloading trucks and vehicles
- Handling incoming goods
- Maintenance
- Lock smith
- Compatible with consumer and industrial touchscreens

HyFlex®

ADVANCED MECHANICAL PROTECTION

11-735

Tough and durable cut protection with a breathable, soft liner

Key Features

- **INTERCEPT™ Cut Resistance Technology:** Advanced personal protection
- **Palm-dipped PU coating:** Excellent grip and abrasion resistance
- **10G lightweight plaited liner:** Soft, flexible, Lycra®-imbued comfort

Vulcanization Chemical Accelerators

- Natural rubber proteins (in knitwrist elastic)

Only a very small number of users may be sensitive to this ingredient(s) and hence may develop irritant and/or allergic contact reactions.

Performance Standards & Regulatory Compliance



Technologies

 **INTERCEPT™**
Cut Resistance Technology



Specifications

BRAND STYLE	DESCRIPTION	Gauge	SIZE	LENGTH	COATING COLOR	PACKAGE
HyFlex® 11-735	Finishing: Palm Coated Coating Material: Polyurethane Liner Material: Fiber glass, HPPE, Nylon, Spandex Cuff Style: Knitwrist	10	6, 7, 8, 9, 10, 11	224-269 mm; 8.81-10.59 in	Black	12 pairs/bag, 12 bags/carton

For additional information visit us at www.ansell.com, or call us at

Europe, Middle East & Africa Region

Ansell Healthcare Europe NV
Riverside Business Park
Blvd International, 55
1070 Brussels, Belgium
T: +32 (0) 2 528 74 00
F: +32 (0) 2 528 74 01

North America Region

Ansell Healthcare Products LLC
111 Wood Avenue South,
Suite 900
Iselin, NJ 08830, USA
T: +1 800 800 0444
F: +1 800 800 0445

Australia

Ansell Limited
Level 3,678 Victoria Street,
Richmond, Vic, 3121
Australia
T: +61 1800 337 041
F: +61 1800 803 578

Asia Pacific Region

Ansell Global Trading Center
(Malaysia) Sdn Bhd
Prima 6, Prima Avenue
Block 3512, Jalan Teknokrat 6
T: +603 8310 6688
F: +603 8310 6699

Latin America & Caribbean Region

Ansell Commercial Mexico S.A. de C.V.
Blvd. Bernardo Quintana No. 7001-C,
Q7001 Torre II,
Suites 1304, 1305 y 1306,
Col. Centro Sur, c.p. 76079
Queretaro, Qro. Mexico
T: +52 442 248 1544 / 248 3133

Canada

Ansell Canada
105 Lauder
Cowansville, QC J2K 2K8
Canada
T: +1 800 363 8340
F: +1 800 267 3551

Ansell, ® and ™ are trademarks owned by Ansell Limited or one of its affiliates. US Patented and US and non-US Patents Pending: www.ansell.com/patentmarking © 2024 Ansell Limited. All Rights Reserved.

Neither this document nor any other statement made herein by or on behalf of Ansell should be construed as a warranty of merchantability or that any Ansell product is fit for a particular purpose. Ansell assumes no responsibility for the suitability or adequacy of an end user's selection of gloves for a specific application.

