

HyFlex®

ADVANCED MECHANICAL PROTECTION

11-738

The 1st INTERCEPT® Cut Resistant Glove with targeted reinforcement in high wear areas



Cut



Medium Duty

Highly durable cut-resistant gloves, with strong blended fibers and reinforced thumb crotch

- **Heightened defenses:** HyFlex® 11-738 industrial gloves' INTERCEPT Cut Resistance Technology yarn, blended with nylon, Lycra and strengthened fibers provide high cut resistance
- **Advanced durability:** FORTIX™ Abrasion Resistance Technology delivers long-lasting durability
- **Targeted protection:** HyFlex® 11-738 safety gloves' reinforced thumb crotch results in 12x greater resilience than unreinforced competitor gloves
- **Elevated comfort:** Water-based polyurethane and nitrile coating improves grip, while enhancing comfort and dexterity
- **Certified skin-friendly and harm-free:** They are Dermatest®-approved, solvent-free, and OekoTex®-certified for no harmful substances
- **Silicone-free:** HyFlex® 11-738 PPE gloves are silicone-free, preventing contaminant transfer to metal before painting



Industries

- Automotive
- Machinery and Equipment
- Metal fabrication
- Automotive Aftermarket
- Utilities
- Warehousing

Applications

- Handling of sharp-edged objects, pre-assembling, cutting of small dry or lightly oiled parts and maintenance
- Handling of glass sheets, sharp edged objects
- Handling of metal sheets, cutting of dry, painted or galvanised pieces

HyFlex®

ADVANCED MECHANICAL PROTECTION

11-738

The 1st INTERCEPT® Cut Resistant Glove with targeted reinforcement in high wear areas

Key Features

- INTERCEPT™ Cut Resistance and strong fibers: Robust cut protection
- FORTIX™ Abrasion Resistance: PPE gloves with heightened durability
- Reinforced thumb crotch: Targeted hand protection and resilience

Vulcanization Chemical Accelerators

- Zinc Dibutyldithiocarbamate

Only a very small number of users may be sensitive to this ingredient(s) and hence may develop irritant and/or allergic contact reactions.

Technologies



DMF free



FORTIX™

Abrasion Resistance Technology



INTERCEPT™

Cut Resistance Technology



Performance Standards & Regulatory Compliance



ANSI/ISEA 105-2024



EN388: 2016



4X42D



STANDARD 100

4419CIT CITEVE

Specifications

BRAND STYLE	DESCRIPTION	Gauge	SIZE	LENGTH	COATING COLOR	PACKAGE
HyFlex® 11-738	Finishing: Palm Coated Coating Material: Water-Based polyurethane and nitrile Liner Material: Fiber glass, HPPE, Polyester, Spandex Cuff Style: Knitwrist	13	6, 7, 8, 9, 10	225-275 mm; 8.85-10.82 inches	Black	12 pairs/bag, 12 bags/carton

For additional information visit us at www.ansell.com, or call us at

Europe, Middle East & Africa Region

Ansell Healthcare Europe NV
 Riverside Business Park
 Blvd International, 55
 1070 Brussels, Belgium
 T: +32 (0) 2 528 74 00
 F: +32 (0) 2 528 74 01

North America Region

Ansell Healthcare Products LLC
 111 Wood Avenue South,
 Suite 900
 Iselin, NJ 08830, USA
 T: +1 800 800 0444
 F: +1 800 800 0445

Australia

Ansell Limited
 Level 3,678 Victoria Street,
 Richmond, Vic, 3121
 Australia
 T: +61 1800 337 041
 F: +61 1800 803 578

Asia Pacific Region

Ansell Global Trading Center
 (Malaysia) Sdn Bhd
 Prima 6, Prima Avenue
 Block 3512, Jaijan Teknokrat 6
 T: +603 8310 6688
 F: +603 8310 6699

Latin America & Caribbean Region

Ansell Commercial Mexico S.A. de C.V.
 Blvd. Bernardo Quintana No. 7001-C,
 Q7001 Torre II,
 Suites 1304, 1305 y 1306,
 Col. Centro Sur, c.p. 76079
 Queretaro, Qro. Mexico
 T: +52 442 248 1544 / 248 3133

Canada

Ansell Canada
 105 Lauder
 Cowansville, QC J2K 2K8
 Canada
 T: +1 800 363 8340
 F: +1 800 267 3551

Ansell®, and ™ are trademarks owned by Ansell Limited or one of its affiliates. US Patented and US and non-US Patents Pending: www.ansell.com/patentmarking © 2024 Ansell Limited. All Rights Reserved.

Neither this document nor any other statement made herein by or on behalf of Ansell should be construed as a warranty of merchantability or that any Ansell product is fit for a particular purpose. Ansell assumes no responsibility for the suitability or adequacy of an end user's selection of gloves for a specific application.

