

Previously known as: Hylite™



Oil



Medium Duty

## Three quarter-dipped nitrile-coated work gloves, for mechanical resistance, flexibility and comfort

- **Optimized comfort and ergonomics:** With a design shaped to natural hand contours, interlock knit lining, and generous sizing, ActivArm<sup>®</sup> Hylite™ 47-400 three quarter-dipped nitrile-coated work gloves offer superb comfort
- **Advanced protection:** These industrial gloves' special nitrile formulation combines strong mechanical protection, abrasion resistance and oil repellency with high levels of flexibility
- **Enhanced durability:** They outwear cotton alternatives by a margin of 12 to 1, light leather gloves by 5 to 1 and PVC-coated gloves by 3 to 1
- **Reduced surface defect risks:** Containing no silicone, these robust ActivArm<sup>®</sup> gloves are ideal for metal sheet handling and motor manufacture, with assured cleanliness and minimal risks of contaminant transfer



### Industries

- Automotive
- Machinery and Equipment
- Metal fabrication

### Applications


- Handling metal sheets & panels
- Chassis assembly, body trimming
- Final assembly
- Inspection (picking, checking and marking)
- Cutting glasses, sheets, panels
- Fabricating metal parts, glass sheets
- Assembly & inspection of components

Previously known as: Hylite™

### Key Features

- **Contoured design with interlock knit lining:** Optimal comfort and ergonomics
- **Nitrile formulation:** Oil repellency, flexibility and abrasion resistance
- **Silicone-free design:** Clean, contaminant-free metal handling

### Performance Standards & Regulatory Compliance



### Specifications

| BRAND   STYLE             | DESCRIPTION   | Gauge | SIZE        | LENGTH                         | COATING COLOR | PACKAGE                      |
|---------------------------|---|-------|-------------|--------------------------------|---------------|------------------------------|
| ActivArmr® Hylite™ 47-400 | <b>Finishing:</b> ¾ Dipped<br><b>Coating Material:</b> Nitrile<br><b>Liner Material:</b> Interlock cotton<br><b>Cuff Style:</b> Knitwrist | N/A   | 7, 8, 9, 10 | 265-295 mm; 10.74-11.37 inches | Blue          | 12 pairs/bag, 12 bags/carton |

For additional information visit us at [www.ansell.com](http://www.ansell.com), or call us at

#### Europe, Middle East & Africa Region

Ansell Healthcare Europe NV  
 Riverside Business Park  
 Blvd International, 55  
 1070 Brussels, Belgium  
 T: +32 (0) 2 528 74 00  
 F: +32 (0) 2 528 74 01

#### North America Region

Ansell Healthcare Products LLC  
 111 Wood Avenue South,  
 Suite 900  
 Iselin, NJ 08830, USA  
 T: +1 800 800 0444  
 F: +1 800 800 0445

#### Australia

Ansell Limited  
 Level 3, 678 Victoria Street,  
 Richmond, Vic, 3121  
 Australia  
 T: +61 1800 337 041  
 F: +61 1800 803 578

#### Asia Pacific Region

Ansell Global Trading Center  
 (Malaysia) Sdn Bhd  
 Prima 6, Prima Avenue  
 Block 3512, Jaijan Teknokrat 6  
 T: +603 8310 6688  
 F: +603 8310 6699

#### Latin America & Caribbean Region

Ansell Commercial Mexico S.A. de C.V.  
 Blvd. Bernardo Quintana No. 7001-C,  
 Q7001 Torre II,  
 Suites 1304, 1305 y 1306,  
 Col. Centro Sur, c.p. 76079  
 Queretaro, Qro. Mexico  
 T: +52 442 248 1544 / 248 3133

#### Canada

Ansell Canada  
 105 Lauder  
 Cowansville, QC J2K 2K8  
 Canada  
 T: +1 800 363 8340  
 F: +1 800 267 3551

Ansell, ® and ™ are trademarks owned by Ansell Limited or one of its affiliates. US Patented and US and non-US Patents Pending: [www.ansell.com/patentmarking](http://www.ansell.com/patentmarking) © 2024 Ansell Limited. All Rights Reserved.

Neither this document nor any other statement made herein by or on behalf of Ansell should be construed as a warranty of merchantability or that any Ansell product is fit for a particular purpose. Ansell assumes no responsibility for the suitability or adequacy of an end user's selection of gloves for a specific application.