

# HyFlex<sup>®</sup>

ADVANCED MECHANICAL PROTECTION

## 11-571

20% lighter design\* with powerful cut protection



Cut



Light Duty

## Our lightest ANSI/ISEA 105-2024 CUT A4 and EN ISO D glove\* offering 3x greater cut resistance\*\*

- **Enhanced comfort:** The ultra-lightweight design of the HyFlex<sup>®</sup> 11-571 makes this ANSI/ISEA 105-2024 CUT A4 and EN ISO D industrial glove 20% lighter\* without harsh materials
- **Heightened defenses:** 3 times greater cut resistance\*\* using Next Generation single HPPE yarn developed with INTERCEPT<sup>™</sup> Cut Resistance Technology for reliable hand protection
- **Increased Durability for Extended Use:** Improved FORTIX<sup>™</sup> Technology delivers up to 20% more abrasion resistance for longer lasting handling in abrasive conditions\*\*\*
- **Touchscreen Compatible/ ESD:** Allows the wearer to work multiple touchscreen devices while keeping gloves on

\*Versus standard ANSI/ISEA 105-2024 CUT A4 and EN ISO D rated gloves

\*\* Versus similar gloves made of standard HPPE yarn

\*\*\* Versus previous technology version



### Industries

- Automotive
- Machinery and Equipment
- Metal fabrication
- Aerospace

### Applications

- Assembly of sharp parts
- Handling sharp metal parts
- Light duty stamping
- Maintenance

# HyFlex®

ADVANCED MECHANICAL PROTECTION

## 11-571

20% lighter design\* with powerful cut protection

### Key Features

- **Ultra-lightweight design:** 20% lighter\* for unparalleled comfort and dexterity
- **ANSI/ISEA 105-2024 CUT A4 and EN ISO D:** 3x greater cut resistance\*\*
- **Improved FORTIX™ Technology:** up to 20% greater durability\*\*\*

\* Versus standard ANSI/ISEA 105-2024 CUT A4 and EN ISO D rated gloves

\*\* Versus similar gloves made of standard HPPE yarn

\*\*\* Versus previous technology version

### Technologies

 **FORTIX™**  
Abrasion Resistance Technology

 **INTERCEPT™**  
Cut Resistance Technology



**Touchscreen Compatible**

### Performance Standards & Regulatory Compliance



4X43D



ANSI/ISEA 105-2024



4X43D



X1XXXX

### Specifications

BRAND   STYLE	DESCRIPTION	Gauge	SIZE	LENGTH	COATING COLOR	PACKAGE
HyFlex® 11-571	<b>Finishing:</b> Palm dipped, Thumbcrotch reinforcement <b>Coating Material:</b> Nitrile <b>Liner Material:</b> HPPE, Carbon, Nylon, Spandex <b>Cuff Style:</b> Knitwrist	15	5, 6, 7, 8, 9, 10, 11, 12	205mm - 272mm	Black	12 pairs/bag, 12 bags/carton

For additional information visit us at [www.ansell.com](http://www.ansell.com), or call us at

#### Europe, Middle East & Africa Region

Ansell Healthcare Europe NV  
Riverside Business Park  
Blvd International, 55  
1070 Brussels, Belgium  
T: +32 (0) 2 528 74 00  
F: +32 (0) 2 528 74 01

#### North America Region

Ansell Healthcare Products LLC  
111 Wood Avenue South,  
Suite 900  
Iselin, NJ 08830, USA  
T: +1 800 800 0444  
F: +1 800 800 0445

#### Australia

Ansell Limited  
Level 3,678 Victoria Street,  
Richmond, Vic, 3121  
Australia  
T: +61 1800 337 041  
F: +61 1800 803 578

#### Asia Pacific Region

Ansell Global Trading Center  
(Malaysia) Sdn Bhd  
Prima 6, Prima Avenue  
Block 3512, Jaijan Teknokrat 6  
T: +603 8310 6688  
F: +603 8310 6699

#### Latin America & Caribbean Region

Ansell Commercial Mexico S.A. de C.V.  
Blvd. Bernardo Quintana No. 7001-C,  
Q7001 Torre II,  
Suites 1304, 1305 y 1306,  
Col. Centro Sur, c.p. 76079  
Queretaro, Qro. Mexico  
T: +52 442 248 1544 / 248 3133

#### Canada

Ansell Canada  
105 Lauder  
Cowansville, QC J2K 2K8  
Canada  
T: +1 800 363 8340  
F: +1 800 267 3551

Ansell, ® and ™ are trademarks owned by Ansell Limited or one of its affiliates. US Patented and US and non-US Patents Pending: [www.ansell.com/patentmarking](http://www.ansell.com/patentmarking) © 2024 Ansell Limited. All Rights Reserved.

Neither this document nor any other statement made herein by or on behalf of Ansell should be construed as a warranty of merchantability or that any Ansell product is fit for a particular purpose. Ansell assumes no responsibility for the suitability or adequacy of an end user's selection of gloves for a specific application.