

Previously known as: PowerFlex® 80-813



Heat



Cut



Electrical



Medium Duty

## Comfortable flame-resistant gloves, offering advanced arc flash and cut protection

- **Specialized protection:** ActivArm® 80-813 heat-resistant gloves are tested against CGSB 155.20-2000 FR standards, boasting an industry-leading Arc Flash Hazard/Risk Category 1 design that guards against electrical arc flash hazards
- **Advanced defenses:** They feature an aramid composite yarn and thin 13g knitted liner, delivering EN ISO C/ANSI A4-level cut resistance and protecting hands by enabling safe sharp component handling
- **Augmented dexterity:** ActivArm® 80-813 industrial gloves' patented technology and ergonomic design ensure superb flexibility and hand protection
- **Enhanced grip:** Thanks to their proprietary soft foam coating, they make for better grip gloves, reducing slippage and tension in the hands and guaranteeing secure grip performance in wet, oily and dry environments



#### Industries

- Machinery and Equipment
- Mining
- Oil and gas
- Automotive
- Automotive Aftermarket
- Utilities

#### Applications

- Job tasks with potential for arc-flash or flash-flame exposure
- De-energized electrical equipment panels
- Electrical equipment operation and switching\_NFPA 70E\_
- Facility and machinery maintenance
- Handling sharp metal or objects

Previously known as: PowerFlex® 80-813

#### Key Features

- **Flame-resistant materials:** Satisfies CGSB 155.20-2000 FR standards
- **Superior arc-flash protection:** Arc Category level 1 per ASTM F2675-22
- **Cut-resistant aramid yarn:** Advanced cut protection

#### Vulcanization Chemical Accelerators

- Zinc Dibutyldithiocarbamate

Only a very small number of users may be sensitive to this ingredient(s) and hence may develop irritant and/or allergic contact reactions.

#### Performance Standards & Regulatory Compliance

ANSI/ISEA 105-2024



EN388: 2016



2X42C

EN 407



412100

#### Specifications

BRAND   STYLE	DESCRIPTION	Gauge	SIZE	LENGTH	COATING COLOR	PACKAGE
ActivArm® 80-813	<b>Finishing:</b> Palm Coated <b>Coating Material:</b> Neoprene Foam <b>Liner Material:</b> Fiber glass, Modacrylic, Aramid <b>Cuff Style:</b> Knitwrist	13	6, 7, 8, 9, 10, 11	225-260 mm; 8.86-10.24 inches	Black	12 pairs/bag, 12 bags/carton

#### For additional information visit us at [www.ansell.com](http://www.ansell.com), or call us at

##### Europe, Middle East & Africa Region

Ansell Healthcare Europe NV  
 Riverside Business Park  
 Blvd International, 55  
 1070 Brussels, Belgium  
 T: +32 (0) 2 528 74 00  
 F: +32 (0) 2 528 74 01

##### North America Region

Ansell Healthcare Products LLC  
 111 Wood Avenue South,  
 Suite 900  
 Iselin, NJ 08830, USA  
 T: +1 800 800 0444  
 F: +1 800 800 0445

##### Australia

Ansell Limited  
 Level 3, 678 Victoria Street,  
 Richmond, Vic, 3121  
 Australia  
 T: +61 1800 337 041  
 F: +61 1800 803 578

##### Asia Pacific Region

Ansell Global Trading Center  
 (Malaysia) Sdn Bhd  
 Prima 6, Prima Avenue  
 Block 3512, Jalan Teknokrat 6  
 T: +603 8310 6688  
 F: +603 8310 6699

##### Latin America & Caribbean Region

Ansell Commercial Mexico S.A. de C.V.  
 Blvd. Bernardo Quintana No. 7001-C,  
 Q7001 Torre II,  
 Suites 1304, 1305 y 1306,  
 Col. Centro Sur, c.p. 76079  
 Queretaro, Qro. Mexico  
 T: +52 442 248 1544 / 248 3133

##### Canada

Ansell Canada  
 105 Lauder  
 Cowansville, QC J2K 2K8  
 Canada  
 T: +1 800 363 8340  
 F: +1 800 267 3551

Ansell, ® and ™ are trademarks owned by Ansell Limited or one of its affiliates. US Patented and US and non-US Patents Pending: [www.ansell.com/patentmarking](http://www.ansell.com/patentmarking) © 2024 Ansell Limited. All Rights Reserved.

Neither this document nor any other statement made herein by or on behalf of Ansell should be construed as a warranty of merchantability or that any Ansell product is fit for a particular purpose. Ansell assumes no responsibility for the suitability or adequacy of an end user's selection of gloves for a specific application.