



Cut



Medium Duty

## Medium-duty cut-resistant gloves, combining grip with abrasion and vibration resistance

- **Reinforced protection:** ActivArmr® 97-003 safety gloves feature INTERCEPT™ Cut Resistance Technology, fused with Kevlar® and stainless steel fibers, for protective gloves that deliver ANSI A4/EN ISO D cut protection and six times greater laceration defenses than standard leather glove alternatives\*
- **Enhanced defenses and grip:** Gel padding reduces vibration and impacts, while nitrile foam coating makes for excellent grip in both wet and dry conditions
- **Heightened comfort:** Designed with ZONZ™ Comfort Fit Technology, ActivArmr® 97-003 safety work gloves boast an ergonomic, breathable design, equipped with adjustable Velcro® cuffs for increased dexterity  
\*Based on an internal study comparing standard leather gloves with alternatives designed with ActivArmr® liner and INTERCEPT™ Technology (3/11)



### Industries

- Mining
- Oil and gas

### Applications

- Positioning
- Operating of heavy machinery
- Scaffolding
- Hydraulic set and testing
- Crushing and unloading ore
- Primary grinding
- Hydraulic repair
- Product inspection
- Conveyer and longwall maintenance
- General pumping work
- Handling of tools
- Valve - line maintenance and repair
- Handling jagged metal
- Equipment maintenance Scaffolding Pipe handling and insulation Plumbing and sand blasting
- Heavy machine operation

## Key Features

- **INTERCEPT™ Cut Resistance Technology:** ANSI/ISEA 105-2024 CUT A4 and EN ISO D resistance\*
- **Gel padding:** For industrial gloves that reduce vibrations and impacts
- **ZONZ™ Comfort Fit Technology:** Enhanced fit, feel and wearer comfort  
\*6x greater than standard leather glove alternatives

## Vulcanization Chemical Accelerators

- Zinc Diethyldithiocarbamate

Only a very small number of users may be sensitive to this ingredient(s) and hence may develop irritant and/or allergic contact reactions.

## Performance Standards & Regulatory Compliance

ANSI/ISEA 105-2024



EN388: 2016



4X31D

## Specifications

BRAND   STYLE	DESCRIPTION	Gauge	SIZE	LENGTH	PACKAGE
ActivArm <sup>®</sup> 97-003	<b>Finishing:</b> Palm Coated <b>Coating Material:</b> Foam Nitrile <b>Liner Material:</b> Nylon, Spandex, Stainless steel, Kevlar <sup>®</sup> <b>Cuff Style:</b> Velcro <sup>®</sup>	13	9, 10, 11	269-278 mm	12 pairs/carton

## Technologies



**INTERCEPT™**  
Cut Resistance Technology

## For additional information visit us at [www.ansell.com](http://www.ansell.com), or call us at

### Europe, Middle East & Africa Region

Ansell Healthcare Europe NV  
Riverside Business Park  
Blvd International, 55  
1070 Brussels, Belgium  
T: +32 (0) 2 528 74 00  
F: +32 (0) 2 528 74 01

### North America Region

Ansell Healthcare Products LLC  
111 Wood Avenue South,  
Suite 900  
Iselin, NJ 08830, USA  
T: +1 800 800 0444  
F: +1 800 800 0445

### Australia

Ansell Limited  
Level 3, 678 Victoria Street,  
Richmond, Vic, 3121  
Australia  
T: +61 1800 337 041  
F: +61 1800 803 578

### Asia Pacific Region

Ansell Global Trading Center  
(Malaysia) Sdn Bhd  
Prima 6, Prima Avenue  
Block 3512, Jalan Teknokrat 6  
T: +603 8310 6688  
F: +603 8310 6699

### Latin America & Caribbean Region

Ansell Commercial Mexico S.A. de C.V.  
Blvd. Bernardo Quintana No. 7001-C,  
Q7001 Torre II,  
Suites 1304, 1305 y 1306,  
Col. Centro Sur, c.p. 76079  
Queretaro, Qro. Mexico  
T: +52 442 248 1544 / 248 3133

### Canada

Ansell Canada  
105 Lauder  
Cowansville, QC J2K 2K8  
Canada  
T: +1 800 363 8340  
F: +1 800 267 3551

Ansell, ® and ™ are trademarks owned by Ansell Limited or one of its affiliates. US Patented and US and non-US Patents Pending: [www.ansell.com/patentmarking](http://www.ansell.com/patentmarking) © 2025 Ansell Limited. All Rights Reserved.

Neither this document nor any other statement made herein by or on behalf of Ansell should be construed as a warranty of merchantability or that any Ansell product is fit for a particular purpose. Ansell assumes no responsibility for the suitability or adequacy of an end user's selection of gloves for a specific application.