

ACTIVARMR™

Electrical Insulating Gloves Class 0 - RIG014B

Ergonomically designed natural rubber insulating gloves for all-day safety and comfort

Previously known as: E016B



Electrical



Light Duty

Durable, form-fitting electrical safety gloves, offering flexible, comfortable hand protection*

- **Heightened flexibility and durability:** ActivArm[™] Electrical Insulating Gloves Class 0 - RIG014B are made from natural rubber latex (through an eco-conscious dipping process), for electrical safety gloves that are both durable and flexible
- **Advanced ergonomics:** These insulated rubber gloves' non-splayed fingers and hand-at-rest design minimize hand fatigue
- **Elevated comfort:** A spacious flared cuff ensures plentiful room for clothing and ventilation
- **Specialized defenses:** These electrical gloves are arc flash certified (APC 1 in combination with 96-002 leather gloves)*, can withstand a touch voltage AC maximum of 1000 V (DC maximum 1500) and tolerate acid, ozone and very low temperatures**
- **Increased practicality:** A smooth, case-hardened finish makes for easy donning and doffing
- **Certified protection:** As electrical PPE, they also comply with relevant CSA, NFPA and OSHA standards
*ATPV : 19 cal/cm² EBT : 47 cal/cm² with 96-002 leather gloves
**Category A, Z and C respectively



Industries

- Automotive
- Construction
- Energy

Applications

- Applications with risk of touch voltage
- Electrical Contractors
- Hybrid engine manufacturing and repair
- Maintenance Repairs and Operations in all industrial environments (MRO)
- Mass Transit Repair and Maintenance
- Power maintenance, repair & transmission
- Telecom repair near electrical wires



Electrical Insulating Gloves Class 0 - RIG014B

Ergonomically designed natural rubber insulating gloves for all-day safety and comfort

Previously known as: E016B

Key Features

- ◊ **Natural rubber latex formulation:** Flexibility and durability ensured
- ◊ **Ergonomic design:** For hand protection with minimal fatigue
- ◊ **Generous flared cuff:** Ideal space for clothing and ventilation
*Arc flash certified as per IEC 614821-2:2014 and ATSM F2675:2021 standards

Performance Standards & Regulatory Compliance



Specifications

BRAND STYLE	DESCRIPTION	SIZE	LENGTH	COATING COLOR	PACKAGE
ActivArmR Electrical Insulating Gloves Class 0 - RIG014B	Coating Material: Natural Rubber Latex Cuff Style: Straight Cuff with rolled beaded edge	7, 8, 8.5, 9, 9.5, 10, 10.5, 11, 12	360 / 14.17	Black	• 1 pair/pack, 10 pairs/carton

For additional information visit us at www.ansell.com, or call us at

Europe, Middle East & Africa Region

Ansell Healthcare Europe NV
Riverside Business Park
Blvd International, 55
1070 Brussels, Belgium
T: +32 (0) 2 528 74 00
F: +32 (0) 2 528 74 01

North America Region

Ansell Healthcare Products LLC
111 Wood Avenue South,
Suite 900
Iselin, NJ 08830, USA
T: +1 800 800 0444
F: +1 800 800 0445

Australia

Ansell Limited
Level 3, 678 Victoria Street,
Richmond, Vic, 3121
Australia
T: +61 1800 337 041
F: +61 1800 803 578

Asia Pacific Region

Ansell Global Trading Center
(Malaysia) Sdn Bhd
Prima 6, Prima Avenue
Block 3512, Jalan Teknokrat 6
T: +603 8310 6688
F: +603 8310 6699

Latin America & Caribbean Region

Ansell Commercial Mexico S.A. de C.V.
Blvd. Bernardo Quintana No. 7001-C,
Q7001 Torre II,
Suites 1304, 1305 y 1306,
Col. Centro Sur, c.p. 76079
Queretaro, Qro. Mexico
T: +52 442 248 1544 / 248 3133

Canada

Ansell Canada
105 Lauder
Cowansville, QC J2K 2K8
Canada
T: +1 800 363 8340
F: +1 800 267 3551

Ansell, ® and ™ are trademarks owned by Ansell Limited or one of its affiliates. US Patented and US and non-US Patents Pending: www.ansell.com/patentmarking © 2025 Ansell Limited. All Rights Reserved.

Neither this document nor any other statement made herein by or on behalf of Ansell should be construed as a warranty of merchantability or that any Ansell product is fit for a particular purpose. Ansell assumes no responsibility for the suitability or adequacy of an end user's selection of gloves for a specific application.

