

## EPDM RABS/isolator gloves, designed using premium FDA-approved material, resulting in less frequent glove changes

Port size: 203mm/8"

Thickness: 0.6mm/24 mil

- **Optimized durability:** Designed for repeated autoclave sterilization (up to 50 times), the AlphaTec® EPDM Isolator Glove 85-501 is truly long-lasting
- **Assured protection:** These isolator gloves meet EN ISO 374-1:2016 standards, shielding users from hydrogen peroxide and disinfecting chemicals
- **Extended glove life:** They tolerate frequent oxygen, UV ray and ozone exposure without rapid aging
- **Increased eco-friendliness:** Halogen-free, they can be safely disposed by incineration
- **Food handling compliance:** They conform to FDA Food Contact regulation (FDA Positive List) 21 CFR 177 for Indirect Food Additives



### KEY FEATURES & BENEFITS

- **EPDM composition:** Designed for dexterity and repeated autoclave sterilization
- **Chemical resistance:** Hydrogen peroxide/common disinfecting chemicals
- **Hardy design:** No rapid aging, even with oxygen, UV ray and ozone exposure

### TECHNICAL DATA SHEET

Product Reference	85-501
Material	Ethylene propylene diene rubber_EPDM
Color	Black
Shape	Ambidextrous
External Glove Surface	Smooth
Cuff Style	Beaded
Storage Instructions	Store in a dry and dark environment, temperature of 5°C to 22°C. Retain in original packaging when not in use.
Available Sizes	11, 9.5
Temperature Range	From -20°C to 130°C
Cleanroom Class	Non-Critical Environment
Shelf Life	Three (3) years from date of manufacture.
Tested For Use With Chemotherapy Drugs	No
Standards	CE 0493, EN 388:2016, EN 388:2016 +A1:2018, EN ISO 21420:2020, EN ISO 374-1:2016 Type B, EN ISO 374-1:2016, EN ISO 374-5:2016, EN ISO 374-5:2016, EN 420:2003 + A1:2009, Category III
Vulcanization Chemical Accelerators	<ul style="list-style-type: none"><li>• Diphenyl guanidine</li><li>• Tetramethylthiuram disulfide</li></ul>

### PHYSICAL PROPERTIES

	Typical Values	Testing Method
Typical Length (mm/in)	800/32	EN ISO 21420
Port Size	8"	
Target Single Wall Palm Thickness (mm/mil)	0.60 mm / 24 mil	EN 455-2
Target Single Wall Finger Thickness (mm/mil)	0.60 mm / 24 mil	EN 455-2
Target Single Wall Cuff Thickness (mm/mil)	0.60 mm / 24 mil	EN 455-2

### PROTECTION AGAINST MECHANICAL RISKS, EN 388:2016+A1:2018

Risk	Performance level
Abrasion Resistance	Level 2
Blade Cut Resistance	Level 1
Tear Resistance	Level 1
Puncture Resistance	Level 1
ISO 13997 Cut Resistance	1

### ORDERING INFORMATION

	PORT SIZE	8"/203mm	8"/203mm
	SIZE	9.5	11
85-501	REORDER NO.	85501095	85501110

For additional information visit us at [www.ansell.com](http://www.ansell.com), or call us at

#### Europe, Middle East & Africa Region

Ansell Healthcare Europe NV  
T: +32 (0) 2 528 74 00  
F: +32 (0) 2 528 74 01

#### Asia Pacific Region

Ansell Global Trading Center  
T: +603 8310 6688  
F: +603 8310 6699

#### North America Region

Ansell Healthcare Products LLC  
US T: +1 800 800 0444  
US F: +1 800 800 0445  
CA T: +1-800-363-8340

#### Latin America & Caribbean Region

Ansell Commercial Mexico S.A. de C.V.  
T: +52 442 248 1544 / 248 3133


#### Australia

Ansell Limited  
T: +61 1800 337 041  
F: +61 1800 803 578

#### UK

Ansell Nitritex  
T: +44 1638 663338  
F: +44 1638 668890

### Performance Standards and Regulatory Compliance



Ansell, ® and ™ are trademarks owned by Ansell Limited or one of its affiliates. US Patented and US and non-US Patents Pending: [www.ansell.com/patentmarking](http://www.ansell.com/patentmarking) © 2024 Ansell Limited. All Rights Reserved.

Neither this document nor any other statement made herein by or on behalf of Ansell should be construed as a warranty of merchantability or that any Ansell product is fit for a particular purpose. Ansell assumes no responsibility for the suitability or adequacy of an end user's selection of gloves for a specific application.