



# BioClean™ Clearview Sterile Looped Visor Facemask VFM210-L

## Sterile looped visor face mask, offering advanced bacterial and particle filtration efficiency

- **Advanced defenses:**  
The BioClean™ Clearview Sterile Looped Visor Facemask VFM210-L delivers high bacterial and particle filtration efficiency, for protection of your cleanroom environment you can depend on
- **Enhanced features:** This sterile face mask features a looped design and optically clear visor, with an anti-fog coating, to enable maximized vision
- **Increased comfort:**  
The BioClean™ Clearview Sterile Looped Visor Facemask VFM210-L also offers users breathable comfort

### Key Features and Benefits

- **High bacterial and particle filtration efficiency:** Optimized protection
- **Anti-fog-coated visor:** Unhindered, distortion-free vision



### Industries

- Controlled and Critical Environments
- Laboratory and Research
- Production and Manufacturing

### Recommended For

- Biotechnologies Blending operations
- Clean room cleaning and preparing
- Medical Device Manufacturing
- Preparing pharmaceutical products
- Semiconductor manufacturing
- White goods assembly



# BioClean™ Clearview Sterile Looped Visor Facemask VFM210-L

## TECHNICAL DATA SHEET

### PRODUCT INFORMATION

<b>Material</b>	Polypropylene Polyethylene
<b>Audit Standards</b>	Manufacturing QMS Audit Standards ISO 9001
<b>Standards</b>	ISO 2859, ISO 9001:2015
<b>Packaging Overview</b>	One piece per sealed inner PE bag; 25 inner bags per sealed outer PE bag; four outer bags per lined carton (100 pieces)
<b>Country Of Origin</b>	China
<b>Sterilization Method</b>	Gamma Irradiation
<b>Sterilization Minimum Dose</b>	25kGy
<b>Sterility Assurance Level</b>	10 <sup>-6</sup>
<b>Storage Instructions</b>	Store in a dry, cool place (<40°C) away from direct sunlight and fluorescent light.
<b>Shelf Life</b>	Five (5) years from date of manufacture

### PHYSICAL PROPERTIES

<b>Color</b>	White
<b>String Type</b>	Headloop
<b>Overall Dimensions</b>	WIDTH (± 5mm): 210mm HEIGHT (± 5mm) : 95mm
<b>Inner Facing Layer</b>	Non-woven polypropylene/polyethylene (hydrophilic)
<b>Filtration Layer</b>	Meltblown polyester
<b>Outer Layer</b>	Non-woven spunbonded polyester (hydrophobic)
<b>Fastenings</b>	Non-latex polyurethane loops with plastic clip fastener
<b>Noseband</b>	Plastic coated steel

### PERFORMANCE INFORMATION

<b>Cleanroom Class</b>	Class 10/ISO Class 4 & EU GMP Grade A/B and other sterile cleanrooms
<b>Particle Filtration Efficiency</b>	89.3% @0.1 micron
<b>Bacterial Filtration Efficiency</b>	92.3% @0.3 micron
<b>Viral Filtration Efficiency</b>	93.8% @3.0 micron
<b>Differential Pressure</b>	3.8mm H <sub>2</sub> O/cm <sup>2</sup>

### ORDERING INFORMATION

	<b>SIZE</b>	Looped with blue clip fastener
VFM210-L	REORDER NO.	VFM210-L

For additional information visit us at [www.ansell.com](http://www.ansell.com), or call us at

#### Europe, Middle East & Africa Region

Ansell Healthcare Europe NV  
T: +32 (0) 2 528 74 00  
F: +32 (0) 2 528 74 01

#### Asia Pacific Region

Ansell Global Trading Center  
T: +603 8310 6688  
F: +603 8310 6699

#### North America Region

Ansell Healthcare Products LLC  
US T: +1 800 800 0444  
US F: +1 800 800 0445  
CA T: +1-800-363-8340

#### Latin America & Caribbean Region

Ansell Commercial Mexico S.A. de C.V.  
T: +52 442 248 1544 / 248 3133

#### Australia

Ansell Limited  
T: +61 1800 337 041  
F: +61 1800 803 578

#### UK

Ansell Nitritex  
T: +44 1638 663338  
F: +44 1638 668890

Ansell, ® and ™ are trademarks owned by Ansell Limited or one of its affiliates. US Patented and US and non-US Patents Pending; [www.ansell.com/patentmarking](http://www.ansell.com/patentmarking) © 2025 Ansell Limited. All Rights Reserved.

Neither this document nor any other statement made herein by or on behalf of Ansell should be construed as a warranty of merchantability or that any Ansell product is fit for a particular purpose. Ansell assumes no responsibility for the suitability or adequacy of an end user's selection of gloves for a specific application.

