

# HyFlex®

ADVANCED MECHANICAL PROTECTION

## 11-581

20% lighter design\* with powerful cut protection



Cut



Light Duty

## Our lightest\* glove, meeting ANSI/ISEA 105-2024 CUT A6 and EN ISO F standards, offers 6 times greater cut resistance.\*\*

- **Elevated comfort:** HyFlex® 11-581 industrial gloves boast an ultra-lightweight design, providing ANSI/ISEA 105-2024 CUT A6 and EN ISO F protection at 20% less weight\* that ensures superior cut resistance and enhanced dexterity
- **Heightened defenses:** 6 times greater cut resistance\*\* using Next Generation single HPPE yarn developed with INTERCEPT™ Cut Resistance Technology for reliable hand protection
- **Excellent grip:** Featuring FORTIX™ Technology and thumb crotch reinforcement, these hand protection gloves ensure safer handling in abrasive conditions
- **Increased convenience:** In addition, HyFlex® 11-581 protective gloves allow wearers to work with multiple touchscreen devices while keeping them on



\* Compared to standard ANSI/ISEA 105-2024 CUT A6 and EN ISO F rated gloves

\*\* Compared to similar gloves made of standard HPPE yarn

### Industries

- Automotive
- Machinery and Equipment
- Metal fabrication
- Aerospace

### Applications

- Assembly of sharp parts
- Handling sharp metal parts
- Light duty stamping
- Maintenance

# HyFlex®

ADVANCED MECHANICAL PROTECTION

## 11-581

20% lighter design\* with powerful cut protection

### Key Features

- **Ultra-lightweight design:** 20% lighter\* for unparalleled comfort and dexterity
- **ANSI/ISEA 105-2024 CUT A6 and EN ISO F Protection:** Offers 6x the cut resistance\*\*
- **Thumb crotch reinforcement:** Ideal for dry and slightly oily applications

\* Compared to standard ANSI/ISEA 105-2024 CUT A6 and EN ISO F rated gloves

\*\* Compared to similar gloves made of standard yarn

### Technologies

 **FORTIX™**  
Abrasion Resistance Technology

 **INTERCEPT™**  
Cut Resistance Technology



**Touchscreen Compatible**

### Performance Standards & Regulatory Compliance

ANSI/ISEA 105-2024



EN388: 2016



3X42F

EN 388



3X42F

EN 16350



### Specifications

BRAND   STYLE	DESCRIPTION	Gauge	SIZE	LENGTH	COATING COLOR	PACKAGE
HyFlex® 11-581	<b>Finishing:</b> Palm dipped, Thumbcrotch reinforcement <b>Coating Material:</b> Nitrile <b>Liner Material:</b> HPPE, Tungsten, Nylon, Spandex <b>Cuff Style:</b> Knitwrist	21	6, 7, 8, 9, 10, 11, 12	205mm-272mm	Black	12 pairs/bag, 12 bags/carton

For additional information visit us at [www.ansell.com](http://www.ansell.com), or call us at

#### Europe, Middle East & Africa Region

Ansell Healthcare Europe NV  
Riverside Business Park  
Blvd International, 55  
1070 Brussels, Belgium  
T: +32 (0) 2 528 74 00  
F: +32 (0) 2 528 74 01

#### North America Region

Ansell Healthcare Products LLC  
111 Wood Avenue South,  
Suite 900  
Iselin, NJ 08830, USA  
T: +1 800 800 0444  
F: +1 800 800 0445

#### Australia

Ansell Limited  
Level 3,678 Victoria Street,  
Richmond, Vic, 3121  
Australia  
T: +61 1800 337 041  
F: +61 1800 803 578

#### Asia Pacific Region

Ansell Global Trading Center  
(Malaysia) Sdn Bhd  
Prima 6, Prima Avenue  
Block 3512, Jaijan Teknokrat 6  
T: +603 8310 6688  
F: +603 8310 6699

#### Latin America & Caribbean Region

Ansell Commercial Mexico S.A. de C.V.  
Blvd. Bernardo Quintana No. 7001-C,  
Q7001 Torre II,  
Suites 1304, 1305 y 1306,  
Col. Centro Sur, c.p. 76079  
Queretaro, Qro. Mexico  
T: +52 442 248 1544 / 248 3133

#### Canada

Ansell Canada  
105 Lauder  
Cowansville, QC J2K 2K8  
Canada  
T: +1 800 363 8340  
F: +1 800 267 3551

Ansell, ® and ™ are trademarks owned by Ansell Limited or one of its affiliates. US Patented and US and non-US Patents Pending: [www.ansell.com/patentmarking](http://www.ansell.com/patentmarking) © 2024 Ansell Limited. All Rights Reserved.

Neither this document nor any other statement made herein by or on behalf of Ansell should be construed as a warranty of merchantability or that any Ansell product is fit for a particular purpose. Ansell assumes no responsibility for the suitability or adequacy of an end user's selection of gloves for a specific application.

