

Black nitrile gloves, for dirt-masking hand protection and superior grip

- **Masks stains:** MICROFLEX[®] 93-252 gloves' black color disguises dirt while enhancing the visibility of light-colored objects
- **Enhanced grip:** A fully textured, non-foaming design offers these powder- and silicone-free nitrile gloves superior grip
- **Proven protection:** These gloves comply with EN ISO 374 Type B chemical resistance standards, providing chemical splash protection
- **Genuine versatility:** These gloves are suitable for various applications, used notably by auto mechanics, maintenance workers and law enforcement officers
- **Food handling compliant:** Also ideal for a wide range of food handling applications



Industries

- Automotive
- Automotive Aftermarket
- Life Sciences
- Machinery and Equipment

Recommended For

- Inspection, selecting, checking parts
- General Purpose Auto Aftermarket
- Use of cleaning tools and robotic equipment
- Oil, fluids and filter change
- Engine transmission and repair
- Tire rotation & changes
- Maintaining lab furniture and equipment
- Sample taking and processing
- Blending, compounding solids and liquids
- Raw material sample collection
- Weighing and dispensing of solid and liquid raw materials
- Inspection (picking, checking and marking)

TECHNICAL DATA SHEET

| Product Information | |
|------------------------|--|
| External Glove Surface | Fully Textured |
| Audit Standards | ISO 13485, ISO 9001 |
| Product Certification | Medical Device Regulation (EU) 2017/745 Class I, Personal Protective Equipment Regulation (EU) 2016/425 Category III risks |
| Packaging Overview | 100 gloves per dispenser 10 dispensers per case 1000 gloves per case |
| Storage Instructions | Keep out of direct sunlight; store in a cool and dry place. Keep away from sources of ozone or ignition. |
| Country Of Origin | Malaysia |
| Product Segmentation | Robust |
| Antistatic | Yes |

PHYSICAL PROPERTIES

| | Typical Values | | Testing Method |
|---|---------------------|--------------------|----------------------|
| Length (mm/inches) | 245 / 9.6 | | ASTM D3767, EN 420 |
| Freedom from Holes (Inspection level I) | 1.5 AQL | | ASTM D5151, EN 455-1 |
| Palm Thickness (mm/mils) | 0.12/4.7 | | ASTM D3767, EN 420 |
| Finger Thickness (mm/mils) | 0.15/5.9 | | ASTM D3767, EN 420 |
| | BEFORE AGING | AFTER AGING | |
| Ultimate Tensile Strength (MPa) | 24 | 20 | ASTM D412 & D573 |
| Elongation at Break (%) | 600 | 500 | ASTM D412 |
| Force at break (N) | 7 | 6 | |

ORDERING INFORMATION

| Size | XS (5.5 - 6) | S (6.5 - 7) | M (7.5 - 8) | L (8.5 - 9) | XL (9.5 - 10) | XXL (10.5 - 11) |
|--------------|--------------|-------------|-------------|-------------|---------------|-----------------|
| Product Code | 93252060 | 93252070 | 93252080 | 93252090 | 93252100 | 93252110 |

Performance Standards and Regulatory Compliance



For additional information visit us at www.ansell.com, or call us at

Europe, Middle East & Africa Region

Ansell Healthcare Europe NV
T: +32 (0) 2 528 74 00
F: +32 (0) 2 528 74 01

Asia Pacific Region

MY +603 8310 6688
apac.medical@ansell.com
CN: +86 21 38275000
infochina@ansell.com
JP: +813 5549 8151
info.medical.jp@ansell.com

North America Region

Ansell Healthcare Products LLC
T: +1 800 800 0444
F: +1 800 800 0445

Latin America & Caribbean Region

BR +55 (11) 3356-3100
latam.medical@ansell.com
MX: +52 442 296 2050
latam.medical@ansell.com
CO: +57 1 288 3247
latam.medical@ansell.com

Australia

Ansell Limited
T: +61 1800 337 041
F: +61 1800 803 578

Russia

Ansell PYC
Ten. +7 495 258 13 16

Ansell, ® and ™ are trademarks owned by Ansell Limited or one of its affiliates. US Patented and US and non-US Patents Pending; www.ansell.com/patentmarking © 2024 Ansell Limited. All Rights Reserved.

Neither this document nor any other statement made herein by or on behalf of Ansell should be construed as a warranty of merchantability or that any Ansell product is fit for a particular purpose. Ansell assumes no responsibility for the suitability or adequacy of an end user's selection of gloves for a specific application.

