

## Chemical-resistant disposable gloves that offer tough chemical resistance and superior comfort

- **Three-layer design:** Three layers ensure superior protection against harsh chemicals
- **Thin mil design:** Designed to be thinner than standard reusable chemical-resistant gloves (7.8 mil) for protection that allows for better dexterity when handling small objects and tools
- **Elevated comfort:** Soft material and ergonomic design offer outstanding fit, feel and flexibility
- **Assured quality:** Their low AQL (0.65) means minimal pinhole defect risks
- **High standards:** Meets EN 374 Type A certified in Europe and KOSHA certified in Korea



### Industries

- Aerospace
- Automotive
- Automotive Aftermarket
- Life Sciences
- Chemical
- Agriculture
- Machinery and Equipment
- Metal fabrication
- Utilities
- Warehousing

### Recommended For

- Inspection, selecting, checking parts
- Assembly and inspection of components
- Equipment repair and maintenance
- Production line support and maintenance
- General Purpose Auto Aftermarket
- Oil, fluids and filter change
- Blending, compounding solids and liquids
- Sample taking and processing
- Transferring liquids and solids between vessels and tanks and process equipment

# TECHNICAL DATA SHEET

Product Information	
External Glove Surface	Textured Fingers
Audit Standards	ISO 9001
Product Certification	Personal Protective Equipment Regulation (EU) 2016/425 Category III risks
Packaging Overview	50 gloves per dispenser 10 dispensers per case 500 gloves per case
Storage Instructions	Keep out of direct sunlight; store in a cool and dry place. Keep away from sources of ozone or ignition.
Country Of Origin	Sri Lanka
Product Segmentation	High Risk
Antistatic	Yes EN1149
Fentanyl Tested	Yes
Silicone Free	Yes

## PHYSICAL PROPERTIES

	Typical Values		Testing Method
Length (mm/inches)	≥ 285 / 11.2		ASTM D3767, EN 420
Freedom from Holes (Inspection level I)	0.65 AQL		ASTM D5151, EN 455-1
Palm Thickness (mm/mils)	0.198 / 7.9		ASTM D3767, EN 420
Finger Thickness (mm/mils)	0.20 / 7.9		ASTM D3767, EN 420
	<b>BEFORE AGING</b>	<b>AFTER AGING</b>	
Ultimate Tensile Strength (MPa)	≥ 14	≥ 14	ASTM D412 & D573
Elongation at Break (%)	≥ 500	≥ 400	ASTM D412
Force at break (N)	≥ 6	≥ 6	EN 455-2

## ORDERING INFORMATION

Size	XS (5.5 - 6)	S (6.5 - 7)	M (7.5 - 8)	L (8.5 - 9)	XL (9.5 - 10)	XXL (10.5 - 11)
Product Code	93260060	93260070	93260080	93260090	93260100	93260110
Retail Pack Catalog №			93260RP080	93260RP090	93260RP100	

## Performance Standards and Regulatory Compliance



For additional information visit us at [www.ansell.com](http://www.ansell.com), or call us at

### Europe, Middle East & Africa Region

Ansell Healthcare Europe NV  
T: +32 (0) 2 528 74 00  
F: +32 (0) 2 528 74 01

### Asia Pacific Region

MY +603 8310 6688  
apac.medical@ansell.com  
CN: +86 21 38275000  
infochina@ansell.com  
JP: +813 5549 8151  
info.medical.jp@ansell.com

### North America Region

Ansell Healthcare Products LLC  
T: +1 800 800 0444  
F: +1 800 800 0445

### Latin America & Caribbean Region

BR +55 (11) 3356-3100  
latam.medical@ansell.com  
MX: +52 442 296 2050  
latam.medical@ansell.com  
CO: +57 1 288 3247  
latam.medical@ansell.com

### Australia

Ansell Limited  
T: +61 1800 337 041  
F: +61 1800 803 578

### Russia

Ansell PYC  
Ten. +7 495 258 13 16

Ansell, ® and ™ are trademarks owned by Ansell Limited or one of its affiliates. US Patented and US and non-US Patents Pending; [www.ansell.com/patentmarking](http://www.ansell.com/patentmarking) © 2024 Ansell Limited. All Rights Reserved.

Neither this document nor any other statement made herein by or on behalf of Ansell should be construed as a warranty of merchantability or that any Ansell product is fit for a particular purpose. Ansell assumes no responsibility for the suitability or adequacy of an end user's selection of gloves for a specific application.

