

## Nitrile disposable gloves with excellent dexterity, along with enhanced comfort, fit and feel

- **ERGOFORM® Technology:** ERGOFORM™ Design Technology reduces muscle strain during repetitive tasks, improving worker comfort and productivity
- **Black nitrile composition:** Distinctive black color provides contrast while also hiding the appearance of oils, dirt and grime
- **Secure grip:** Textured on the fingertips for a reliable consistent grip, ensuring tactility and secure handling of instruments and materials
- **Comfort and dexterity:** MICROFLEX® Touch 93-7321 nitrile disposable gloves provide excellent dexterity along with enhanced comfort, fit and feel



### Industries

- Automotive
- Automotive Aftermarket
- Chemical
- Correctional Facilities
- Life Sciences
- Machinery and Equipment
- Maintenance
- Manufacturing

### Recommended For

- Inspection, selecting, checking parts
- Laboratory analysis
- Paint shop
- Oil, fluids and filter change
- General Purpose Auto Aftermarket
- Equipment repair and maintenance

# TECHNICAL DATA SHEET

Product Information	
External Glove Surface	Textured Fingers
Audit Standards	21 CFR 820, ISO 13485, ISO 9001
Product Certification	Medical Device Regulation (EU) 2017/745 Class I, Personal Protective Equipment Regulation (EU) 2016/425 Category III risks, EU Food Contact Approved, Arrêté du 09/04/04, EC 2023/2006, EN ISO 21420:2020, EN 421:2010 Radioactive Contamination, EN ISO 374-1:2016 Type B KPT, EN ISO 374-5:2016 Virus, EN 16523-1, ISO 18889:2019 G1, ISO 9001, ISO 13485, ASTM D6319, FDA21 CFR 177-2600-US Food Contact Approved
Packaging Overview	100 gloves per box; 10 boxes per case; 2XL 90 gloves per box; 900 gloves per carton
Storage Instructions	Keep out of direct sunlight; store in a cool and dry place. Keep away from sources of ozone or ignition.
Country Of Origin	China
Product Segmentation	High Touch
Antistatic	No
Silicone Free	No


## PHYSICAL PROPERTIES

	Typical Values		Testing Method
Length (mm/inches)	245 / 9.6		ASTM D6319, EN 455-2
Freedom from Holes (Inspection level I)	1.5 AQL		ASTM D5151, EN 455-1
Palm Thickness (mm/mils)	0.07 / 2.8		ASTM D6319, EN 455-2
Finger Thickness (mm/mils)	0.11 / 4.3		ASTM D6319, EN 455-2
	<b>BEFORE AGING</b>	<b>AFTER AGING</b>	
Ultimate Tensile Strength (MPa)	≥ 18	≥ 16	ASTM D412 & D573
Elongation at Break (%)	≥ 500	≥ 400	ASTM D412 & D573
Force at break (N)	≥ 6	≥ 6	EN 455

## ORDERING INFORMATION

Size	S (6.5 - 7)	M (7.5 - 8)	L (8.5 - 9)	XL (9.5 - 10)	XS (5.5 - 6)	XXL (10.5 - 11)
Product Code	937321070	937321080	937321090	937321100	937321060	937321110

## Performance Standards and Regulatory Compliance



For additional information visit us at [www.ansell.com](http://www.ansell.com), or call us at

**Europe, Middle East & Africa Region**  
 Ansell Healthcare Europe NV  
 T: +32 (0) 2 528 74 00  
 F: +32 (0) 2 528 74 01

**Asia Pacific Region**  
 MY +603 8310 6688  
 apac.medical@ansell.com  
 CN: +86 21 38275000  
 infochina@ansell.com  
 JP: +813 5549 8151  
 info.medical.jp@ansell.com

**North America Region**  
 Ansell Healthcare Products LLC  
 T: +1 800 800 0444  
 F: +1 800 800 0445

**Latin America & Caribbean Region**  
 BR +55 (11) 3356-3100  
 latam.medical@ansell.com  
 MX +52 442 296 2050  
 latam.medical@ansell.com  
 CO: +57 1 288 3247  
 latam.medical@ansell.com

**Australia**  
 Ansell Limited  
 T: +61 1800 337 041  
 F: +61 1800 803 578

**Russia**  
 Ansell PYC  
 Ten. +7 495 258 13 16

Technology



Ansell<sup>®</sup> and <sup>™</sup> are trademarks owned by Ansell Limited or one of its affiliates. US Patented and US and non-US Patents Pending: [www.ansell.com/patentmarking](http://www.ansell.com/patentmarking) © 2025 Ansell Limited. All Rights Reserved.

Neither this document nor any other statement made herein by or on behalf of Ansell should be construed as a warranty of merchantability or that any Ansell product is fit for a particular purpose. Ansell assumes no responsibility for the suitability or adequacy of an end user's selection of gloves for a specific application.

