



Multi Purpose



Light Duty

Our best Multi-Purpose gloves, now made green

- **Sustainable design:** HyFlex® 11-842 sustainable Multi-Purpose glove liners are designed with 30% recycled content* reducing our carbon footprint by 75g CO2eq/pair** and plastic-free inner packaging that contains 70% fewer materials^
- **Increased durability:** FORTIX™ Technology provides up to 20% greater abrasion resistance^^
- **Enhanced comfort:** ZONZ™ Comfort Fit Technology helps improve breathability and dexterity
- **Touchscreen compatibility:** These industrial gloves work with multiple touchscreen devices - no need to remove them when switching between tasks for enhanced workplace safety
- **Certified skin-friendliness:** These HyFlex® gloves are dermatologically tested and free of harmful substances

*30% is the minimum recycled content in final product

**vs. standard nylon multi-purpose gloves
^71% less greenhouse gas emissions - Ansell's LCA, calculated as weight reduction, peer-reviewed

^^vs. previous technology version



Industries

- Automotive
- Automotive Aftermarket
- Industrial
- Machinery and Equipment
- Metal fabrication
- Emergency Medical Services
- Utilities
- Warehousing
- Logistics
- Oil and gas
- Food processing and handling
- Aerospace

Applications

- General handling
- Assembly of small parts
- Raw material handling
- Picking, fastening components
- Adjusting systems and screwing
- Warehouse and logistics operations
- Compatible with consumer and industrial touchscreens
- Quality inspection
- Dry food handling & packaging
- Occasional handling of hot objects : EN407 Contact Heat class 1 (100°C for 15s)

HyFlex®

ADVANCED MECHANICAL PROTECTION

11-842

Sustainable Multi-Purpose glove made with recycled content

Key Features

- **Glove made with 30% recycled content***: Carbon footprint reduction of 75g CO₂eq/pair**
- **FORTIX™ Technology**: Up to 20% greater abrasion resistance^
- **ZONZ™ Comfort Fit Technology**: Better breathability and hand movement

*% is the minimum recycled content in final product

** vs standard nylon Multi-Purpose glove

^vs previous technology version

Technologies



Performance Standards & Regulatory Compliance

ANSI/ISEA 105-2024



EN588: 2016



4131A

EN 407



X1XXXX



STANDARD 100
1408033
Centexbel

Specifications

BRAND STYLE	DESCRIPTION	Gauge	SIZE	LENGTH	COATING COLOR	PACKAGE
HyFlex® 11-842	Finishing: Palm dipped Coating Material: Fortix™ Foam Nitrile Liner Material: Recycled Nylon, Spandex Cuff Style: Knitwrist	15	5, 6, 7, 8, 9, 10, 11	190-275 MM	Black	12 pairs/bag, 12 bags/carton

For additional information visit us at www.ansell.com, or call us at

Europe, Middle East & Africa Region

Ansell Healthcare Europe NV
Riverside Business Park
Blvd International, 55
1070 Brussels, Belgium
T: +32 (0) 2 528 74 00
F: +32 (0) 2 528 74 01

North America Region

Ansell Healthcare Products LLC
111 Wood Avenue South,
Suite 900
Iselin, NJ 08830, USA
T: +1 800 800 0444
F: +1 800 800 0445

Australia

Ansell Limited
Level 3,678 Victoria Street,
Richmond, Vic, 3121
Australia
T: +61 1800 337 041
F: +61 1800 803 578

Asia Pacific Region

Ansell Global Trading Center
(Malaysia) Sdn Bhd
Prima 6, Prima Avenue
Block 3512, Jaijan Teknokrat 6
T: +603 8310 6688
F: +603 8310 6699

Latin America & Caribbean Region

Ansell Commercial Mexico S.A. de C.V.
Blvd. Bernardo Quintana No. 7001-C,
Q7001 Torre II,
Suites 1304, 1305 y 1306,
Col. Centro Sur, c.p. 76079
Queretaro, Qro. Mexico
T: +52 442 248 1544 / 248 3133

Canada

Ansell Canada
105 Lauder
Cowansville, QC J2K 2K8
Canada
T: +1 800 363 8340
F: +1 800 267 3551

Ansell, ® and ™ are trademarks owned by Ansell Limited or one of its affiliates. US Patented and US and non-US Patents Pending: www.ansell.com/patentmarking © 2024 Ansell Limited. All Rights Reserved.

Neither this document nor any other statement made herein by or on behalf of Ansell should be construed as a warranty of merchantability or that any Ansell product is fit for a particular purpose. Ansell assumes no responsibility for the suitability or adequacy of an end user's selection of gloves for a specific application.

