

VIKING

WRS

Lightweight surface rescue suit

Provides protection for personnel who are not divers, but are working on, near or above water.



Industries

- Surface Rescue


Applications

- Flooding applications
- On water rescue
- Swift water rescue

KEY FEATURES & BENEFITS

- Ideal for fire rescue teams, coastguard and environment agency teams
- Extremely lightweight, flexible, durable and puncture resistant material
- Unique “Vulca-Seam Technology” ensures watertight seams
- Smooth outer surface for easy cleaning
- Front entry, non adjustable torso, for ease of operation

Seam Diagram



Performance Standards



Product Information

| Product Information | |
|---------------------------|---|
| Color | Black legs with Yellow top |
| Country Of Origin | Lithuania |
| Product Material | 255 g/m2 Nylon outer / Butyl rubber / Nylon inner material |
| Product Reference | WRS |
| Reinforcements | The VIKING™ WRS material is inherently abrasion and puncture resistant. Additional reinforcements are fitted to knees and elbows as standard. |
| Seam Type | Stitched and Taped |
| Available Sizes | S, M, L, XL, 2XL |
| Standards Overview | Regulation (EU) 2016/425, using applicable parts of EN ISO 15027-1:2017 and EN 14225-2:2017 |

Suit Components & Accessories

| Suit Components and Accessories | |
|------------------------------------|--|
| Design Features | Front entry with non-adjustable torso. No valves fitted. High visibility reflectors are fitted as standard to the zip flap, wrists, upper arms and back of legs. |
| Neck Seal | Fitted with a Surveyor latex neck seal as standard. Option: VIKING™ Quick Neck system, which allows for quick changing of broken seals. |
| Cuffs | Latex conical cuffs are the standard fitment. Options: A rubber cuff ring system or the VIKING™ Bayonet Ring System. Both systems make the fitment of latex gloves possible. |
| Footwear And Attachments | Rubber coated 5 mm neoprene boots. The boots feature a non-slip outsole and a heel fin retainer. Alternative options are available. |
| Zipper | Medium Duty (MD) non-magnetic; 85 or 90 cm long; placed diagonally across the upper body. The zipper is covered by a flap. |
| Included With Each Delivery | Each suit comes supplied with suspenders, carry bag, user manual, repair kit and zip care materials. |

For additional information visit us at www.ansell.com, or call us at

Europe, Middle East & Africa Region

Ansell Healthcare Europe NV
T: +32 (0) 2 528 74 00

North America Region

Ansell Healthcare Products LLC
T: +1 800 800 0444

Australia

Ansell Limited
T: +61 1800 337 041

Asia Pacific Region

Ansell Global Trading Center
T: +603 8310 6688

Latin America & Caribbean Region

Ansell Commercial Mexico S.A. de C.V.
T: +52 442 248 1544 / 248 3133

Ansell, ® and ™ are trademarks owned by Ansell Limited or one of its affiliates. US Patented and US and non-US Patents Pending; www.ansell.com/patentmarking © 2025 Ansell Limited. All Rights Reserved.

Neither this document nor any other statement made herein by or on behalf of Ansell should be construed as a warranty of merchantability or that any Ansell product is fit for a particular purpose. Ansell assumes no responsibility for the suitability or adequacy of an end user's selection of gloves for a specific application.

