

# HyFlex®

ADVANCED MECHANICAL PROTECTION

## HyFlex® 11-757

Our lightest thinnest ANSI A7 / ISO level F cut resistant touchscreen glove



Cut



Light Duty

## Durable lightweight industrial gloves, combining advanced cut resistance with superb comfort

- **Advanced protection:** HyFlex® 11-757 light-duty industrial gloves feature INTERCEPT™ Cut Resistance Technology, offering wearers truly advanced, ANSI A7/EN ISO F\* cut resistance levels
- **Enhanced usability:** Their ultra-light, ultra-thin design ensures ample dexterity, breathable comfort and touchscreen compatibility, for uninterrupted daily use and optimized productivity
- **Improved durability:** These HyFlex® gloves' palm-dipped polyurethane coating also delivers excellent abrasion resistance
- **Considered ergonomics:** With a tailored fit at the base of the pinky finger, these safety gloves are shaped around natural hand contours
- **Assured skin-friendliness:** They have also been dermatologically approved by Dermatest® \*7x greater than standard ANSI A2/EN ISO B-level gloves



### Industries

- Aerospace
- Automotive
- Machinery and Equipment
- Electronics
- Glass manufacturing
- White Goods

### Applications

- Assembly & inspection of components
- Picking, fastening components
- Final assembly
- Applying finish to materials, products
- Applications requiring dexterity and precision
- Handling metal sheets & panels
- Handling of glass sheets, sharp-edged objects

# HyFlex®

ADVANCED MECHANICAL PROTECTION

## HyFlex® 11-757

Our lightest thinnest ANSI A7 / ISO level F cut resistant touchscreen glove

### Key Features

- **INTERCEPT™ Cut Resistance Technology:** Superior cut resistance\*
- **Ultra-thin lightweight design:** Dexterity and touchscreen compatibility
- **Polyurethane (PU) coating:** Excellent abrasion resistance  
\*7x greater than standard ANSI A2/EN ISO B-level gloves

### Technologies



Touchscreen Compatible

### Performance Standards & Regulatory Compliance

ANSI/ISEA 105-2024



EN388: 2016



3X31F

### Specifications

BRAND   STYLE	DESCRIPTION	Gauge	SIZE	LENGTH	COATING COLOR	PACKAGE
HyFlex® 11-757	<b>Finishing:</b> Palm dipped, Thumbcrotch reinforcement <b>Coating Material:</b> Polyurethane <b>Liner Material:</b> Nylon, Stainless steel, Polyester, Tungsten <b>Cuff Style:</b> Knitwrist	18	6, 7, 8, 9, 10, 11	222-274 mm / 8.74 - 10.8 inch	Black	12 pairs/bag, 12 bags/carton

For additional information visit us at [www.ansell.com](http://www.ansell.com), or call us at

#### Europe, Middle East & Africa Region

Ansell Healthcare Europe NV  
Riverside Business Park  
Blvd International, 55  
1070 Brussels, Belgium  
T: +32 (0) 2 528 74 00  
F: +32 (0) 2 528 74 01

#### North America Region

Ansell Healthcare Products LLC  
111 Wood Avenue South,  
Suite 900  
Iselin, NJ 08830, USA  
T: +1 800 800 0444  
F: +1 800 800 0445

#### Australia

Ansell Limited  
Level 3,678 Victoria Street,  
Richmond, Vic, 3121  
Australia  
T: +61 1800 337 041  
F: +61 1800 803 578

#### Asia Pacific Region

Ansell Global Trading Center  
(Malaysia) Sdn Bhd  
Prima 6, Prima Avenue  
Block 3512, Jalan Teknokrat 6  
T: +603 8310 6688  
F: +603 8310 6699

#### Latin America & Caribbean Region

Ansell Commercial Mexico S.A. de C.V.  
Blvd. Bernardo Quintana No. 7001-C,  
Q7001 Torre II,  
Suites 1304, 1305 y 1306,  
Col. Centro Sur, c.p. 76079  
Queretaro, Qro. Mexico  
T: +52 442 248 1544 / 248 3133

#### Canada

Ansell Canada  
105 Lauder  
Cowansville, QC J2K 2K8  
Canada  
T: +1 800 363 8340  
F: +1 800 267 3551

Ansell, ® and ™ are trademarks owned by Ansell Limited or one of its affiliates. US Patented and US and non-US Patents Pending: [www.ansell.com/patentmarking](http://www.ansell.com/patentmarking) © 2024 Ansell Limited. All Rights Reserved.

Neither this document nor any other statement made herein by or on behalf of Ansell should be construed as a warranty of merchantability or that any Ansell product is fit for a particular purpose. Ansell assumes no responsibility for the suitability or adequacy of an end user's selection of gloves for a specific application.

