

Previously known as: MERCURY™43-113



Heat



Welding



Medium Duty

## Heat- and cut-resistant gloves, granting wearers complete hand and wrist protection

- **Advanced protection:** ActivArmr® 43-113 safety gloves feature Dupont™ Kevlar® outer yarn and can intermittently handle dry hot objects up to 350°C/660°F, resisting radiant, convective and contact heat
- **Specialized defenses:** ActivArmr® 43-113 flame-resistant gloves do not melt, drip or propagate flames as they self-extinguish, protecting hands, wrists and arms from serious skin injuries
- **Advanced cut resistance:** They also satisfy ANSI A5/EN ISO E cut resistance standards, making them an ideal choice for handling machinery and equipment
- **Heightened comfort:** ActivArmr® 43-113 protective gloves are cotton-lined, boosting their absorbency and dexterity
- **Enhanced features:** Their long knitwrist cuff also ensures greater forearm and wrist protection



#### Industries

- Machinery and Equipment

#### Applications

- Handling hot glass, bottles and panes
- Handling hot metal castings
- Rubber processing, vulcanizing and calendaring
- Demoulding rubber tyres, belts and profiles
- Removing products from autoclaves

# ACTIVARMR®

PERSONAL PROTECTIVE GEAR

## 43-113

### Heat and Flame Resistant Glove

Previously known as: MERCURY™43-113

#### Key Features

- Dupont™ Kevlar® outer yarn: Tolerates dry handling up to 350°C/660°F
- Self-extinguishing design: For reliably flame-resistant work gloves
- ANSI/ISEA 105-2024 CUT A5 and EN ISO E certification: Offers superb hand protection.

#### Vulcanization Chemical Accelerators

- Natural rubber proteins

Only a very small number of users may be sensitive to this ingredient(s) and hence may develop irritant and/or allergic contact reactions.

#### Performance Standards & Regulatory Compliance

ANSI/ISEA 105-2024



EN388: 2016



EN 407



#### Technologies

# Kevlar®

#### Specifications

BRAND   STYLE	DESCRIPTION	Gauge	SIZE	LENGTH	PACKAGE
ActivArm® 43-113	<b>Liner Material:</b> Kevlar para aramid with silica fiber core <b>Cuff Style:</b> Knitwrist	7	6, 7, 8, 9, 10, 11	330-381 mm/12.99-15 inches	6 pairs/bag, 6 bags/carton

For additional information visit us at [www.ansell.com](http://www.ansell.com), or call us at

#### Europe, Middle East & Africa Region

Ansell Healthcare Europe NV  
Riverside Business Park  
Blvd International, 55  
1070 Brussels, Belgium  
T: +32 (0) 2 528 74 00  
F: +32 (0) 2 528 74 01

#### North America Region

Ansell Healthcare Products LLC  
111 Wood Avenue South,  
Suite 900  
Iselin, NJ 08830, USA  
T: +1 800 800 0444  
F: +1 800 800 0445

#### Australia

Ansell Limited  
Level 3, 678 Victoria Street,  
Richmond, Vic, 3121  
Australia  
T: +61 1800 337 041  
F: +61 1800 803 578

#### Asia Pacific Region

Ansell Global Trading Center  
(Malaysia) Sdn Bhd  
Prima 6, Prima Avenue  
Block 3512, Jalin Teknokrat 6  
T: +603 8310 6688  
F: +603 8310 6699

#### Latin America & Caribbean Region

Ansell Commercial Mexico S.A. de C.V.  
Blvd. Bernardo Quintana No. 7001-C,  
Q7001 Torre II,  
Suites 1304, 1305 y 1306,  
Col. Centro Sur, c.p. 76079  
Queretaro, Qro. Mexico  
T: +52 442 248 1544 / 248 3133

#### Canada

Ansell Canada  
105 Lauder  
Cowansville, QC J2K 2K8  
Canada  
T: +1 800 363 8340  
F: +1 800 267 3551

Ansell, ® and ™ are trademarks owned by Ansell Limited or one of its affiliates. US Patented and US and non-US Patents Pending: [www.ansell.com/patentmarking](http://www.ansell.com/patentmarking) © 2024 Ansell Limited. All Rights Reserved.

Neither this document nor any other statement made herein by or on behalf of Ansell should be construed as a warranty of merchantability or that any Ansell product is fit for a particular purpose. Ansell assumes no responsibility for the suitability or adequacy of an end user's selection of gloves for a specific application.

# Ansell