

## Abrasion-resistant chemical gloves with heightened grip, perfect for indoor application

- **Enhanced grip:** AlphaTec® 58-530W chemical gloves' ANSELL GRIP™ coating means less force is required when handling wet or oily components
- **Elevated comfort:** Their white nylon inner liner enhances comfort and offers excellent durability
- **Advanced defenses:** A bonded construction, whereby their coating polymer doesn't penetrate the liner in manufacture, guarantees EN 374 Type A chemical protection
- **Improved durability:** These AlphaTec® gloves achieve ANSI/ISEA 105-2024 ABRASION LEVEL 5 and EN ABRASION LEVEL 3 standards
- **Specialized protection:** In addition, they offer EN 407 heat resistance, for improved workplace safety
- **Augmented dexterity:** AlphaTec® 58-530W industrial gloves' light 13-gauge design makes them more dexterous, for maneuverable hand protection

### Industries

- Automotive
- Automotive Aftermarket
- Machinery and Equipment
- Metal fabrication
- Chemical
- Oil and gas
- Food Processing

### Applications

- Metalworking & assembly operations
- Body painting including surface inspection
- Applying sealers, touching up
- Changing tools and dies
- Handling application & cleaning tools
- Warehousing of raw materials
- Loading and unloading trucks and vehicles
- Filling, blending and charging of raw materials
- Transferring liquids and solids
- Loading and unloading of process equipment
- Transferring liquids and solids between vessels and tanks and process equipment
- Supervision of running operation
- Handling outgoing goods: cans, vessels, bulkpack and cartons
- Opening furnaces draining pumps valves or lines and crackers BTX process
- Food Processing



# AlphaTec®

ADVANCED CHEMICAL PROTECTION

## 58-530W

Unique combination of grip and chemical resistance

### Key Features

- **ANSELL GRIP™ Technology:** Less force needed to grip wet or oily parts
- **White nylon liner:** Safety gloves with enhanced comfort and durability
- **Bonded construction:** Zero liner penetration, heightened dexterity

### Vulcanization Chemical Accelerators

- Zinc Diethyldithiocarbamate

Only a very small number of users may be sensitive to this ingredient(s) and hence may develop irritant and/or allergic contact reactions.

### Technologies



### Performance Standards

ANSI/ISEA 105-2024



0493

EN388: 2016



3131A

EN 407



XIXXXX

EN ISO 374-1:2016  
Type A



AJKLOPT

EN ISO 374-5:2016



### Specifications

BRAND   STYLE	DESCRIPTION	SIZE	LENGT H	COLOR	PACKAGE
AlphaTec® 58-530W	<b>Liner Material:</b> Nylon <b>Coating Material:</b> Nitrile <b>Featured Technology:</b> ANSELL GRIP™	7, 8, 9, 10, 11	290 / 11.4	Grey	<ul style="list-style-type: none"><li>• 6 pairs/polybag; 12 polybags/carton</li><li>• Vend pack variant ,1 pair per bag,72 bags per carton</li></ul>

#### Europe, Middle East & Africa Region

Ansell Healthcare Europe NV  
Riverside Business Park  
Blvd International, 55  
1070 Brussels, Belgium  
T: +32 (0) 2 528 74 00  
F: +32 (0) 2 528 74 01

#### North America Region

Ansell Healthcare Products LLC  
111 Wood Avenue South,  
Suite 210  
Iselin, NJ 08830, USA  
T: +1 800 800 0444  
F: +1 800 800 0445

#### Latin America & Caribbean Region

Ansell Commercial Mexico S.A. de C.V.  
Blvd. Bernardo Quintana No. 7001-C,  
Q7001 Torre II,  
Suites 1304, 1305 y 1306,  
Col. Centro Sur, c.p. 76079  
Queretaro, Qro. Mexico  
T: +52 442 248 1544 / 248 3133

#### Canada

Ansell Canada Inc.  
105, rue Lauder  
Cowansville (Québec)  
J2K 2K8, Canada  
T: 1 800 363-8340  
F: 1 888 267-3551

Ansell, ® and ™ are trademarks owned by Ansell Limited or one of its affiliates. US Patented and US and non-US Patents Pending: [www.ansell.com/patentmarking](http://www.ansell.com/patentmarking) © 2024 Ansell Limited. All Rights Reserved.

Neither this document nor any other statement made herein by or on behalf of Ansell should be construed as a warranty of merchantability or that any Ansell product is fit for a particular purpose. Ansell assumes no responsibility for the suitability or adequacy of an end user's selection of gloves for a specific application.

