

## Gloves ergonomically designed with exceptional grip

- **ERGOFORM™ Technology:** MICROFLEX<sup>®</sup> 73-847 gloves are designed with proprietary technology to reduce hand fatigue
- **Excellent wet grip:** This neoprene glove has a "grippy" textured outer finish for good grip in wet or dry environments. Certified by U.S. Ergonomics for wet performance\*
- **Comfortable fit and heightened sensitivity:** Soft and pliable neoprene provides tactile sensitivity & comfort for longer periods
- **Reduced allergy risk:** Made without natural rubber proteins and powder to help protect workers from Type 1 (latex) allergies



\*This product was certified by United States Ergonomics as it demonstrated exceptional wet grip performance in a variety of wet grip test conditions — these included gripping tests involving soap solutions, artificial saliva, artificial blood.

### Industries

- Life Sciences

### Recommended For

- Plant disinfection and sanitization
- Maintaining lab furniture and equipment
- Transferring liquids and solids
- Transferring liquids
- Loading centrifuges and chromatography columns
- Assembly of parts
- Sample taking and processing
- Blending, compounding solids and liquids
- Raw material sample collection
- Damp donning

# TECHNICAL DATA SHEET

Product Information	
External Glove Surface	Textured Fingers
Audit Standards	ISO 13485:2003
Packaging Overview	100 gloves per dispenser 10 dispensers per case 1000 gloves per case
Storage Instructions	Keep out of direct sunlight; store in a cool and dry place. Keep away from sources of ozone or ignition.
Country Of Origin	Indonesia
Product Segmentation	Multi-Purpose
Antistatic	No
Vulcanization Chemical Accelerators	<ul style="list-style-type: none"> <li>Zinc Dibutyldithiocarbamate (ZDBC)</li> </ul> <p><i>Only a very small number of users may be sensitive to this ingredient(s) and hence may develop irritant and/or allergic contact reactions.</i></p>


## PHYSICAL PROPERTIES

	Typical Values		Testing Method
Length (mm/inches)	245 / 9.6		ASTM D3767, EN 420
Freedom from Holes (Inspection level I)	1.5 AQL		ASTM D5151, EN 455-1
Palm Thickness (mm/mils)	0.10 / 3.9		ASTM D3767, EN 420
Finger Thickness (mm/mils)	0.13 / 5.1		ASTM D3767, EN 420
	<b>BEFORE AGING</b>	<b>AFTER AGING</b>	
Ultimate Tensile Strength (MPa)	≥ 18	≥ 14	ASTM D412 & D573
Elongation at Break (%)	≥ 500	≥ 400	ASTM D412
Force at break (N)	<6	<6	

## ORDERING INFORMATION

Size	XS (5.5 - 6)	S (6.5 - 7)	M (7.5 - 8)	L (8.5 - 9)	XL (9.5 - 10)
Product Code	73847060	73847070	73847080	73847090	73847100

## Performance Standards and Regulatory Compliance



For additional information visit us at [www.ansell.com](http://www.ansell.com), or call us at

### Europe, Middle East & Africa Region

Ansell Healthcare Europe NV  
T: +32 (0) 2 528 74 00  
F: +32 (0) 2 528 74 01

### Asia Pacific Region

MY +603 8310 6688  
apac.medical@ansell.com  
CN: +86 21 38275000  
infochina@ansell.com  
JP: +813 5549 8151  
info.medical.jp@ansell.com

### North America Region

Ansell Healthcare Products LLC  
T: +1 800 800 0444  
F: +1 800 800 0445

### Latin America & Caribbean Region

BR +55 (11) 3356-3100  
latam.medical@ansell.com  
MX: +52 442 296 2050  
latam.medical@ansell.com  
CO: +57 1 288 3247  
latam.medical@ansell.com

### Australia

Ansell Limited  
T: +61 1800 337 041  
F: +61 1800 803 578

### Russia

Ansell PYC  
Ten. +7 495 258 13 16

Technology



Ansell, ® and ™ are trademarks owned by Ansell Limited or one of its affiliates. US Patented and US and non-US Patents Pending; [www.ansell.com/patentmarking](http://www.ansell.com/patentmarking) © 2024 Ansell Limited. All Rights Reserved.

Neither this document nor any other statement made herein by or on behalf of Ansell should be construed as a warranty of merchantability or that any Ansell product is fit for a particular purpose. Ansell assumes no responsibility for the suitability or adequacy of an end user's selection of gloves for a specific application.

