



Cut



Medium Duty

Durable increased visibility work gloves, designed to protect workers in low-light conditions

- **Specialized protection:** ActivArm[®] 97-013 industrial gloves possess high-visibility features on the palm and back of the hand, with a retro-reflective logo, to ensure wearer safety in dark/low-light conditions
- **Optimized comfort:** With a 13-gauge fiberglass and polyester liner, ActivArm[®] 97-013 safety work gloves keep hands comfortable and sweat-free throughout the day
- **Advanced ergonomics:** These hand protection gloves offer a naturally curved, relaxed fit, for reduced hand fatigue and increased dexterity
- **Improved cut resistance:** They are also designed with INTERCEPT™ Cut Resistance Technology, for better laceration defenses
- **Added grip:** ActivArm[®] 97-013 medium-duty gloves boast excellent grip in both wet and dry working environments



Industries

- Mining
- Oil and gas


Applications

- Signalling/Positioning
- Operating of heavy machinery
- Loading and hauling
- Hydraulic repair
- Shipping and loading of product
- Vehicle Maintenance
- General pumping work
- Preparation of site - set-up and disassembly of tool string
- Set-up of pressure manifold and tubing injector head
- Handling of tools
- Valve - line maintenance and repair
- Handling jagged metal
- Equipment maintenance Scaffolding Pipe handling and insulation Plumbing and sand blasting
- Heavy machine operation

Key Features

- **Extra visibility back and palm:** Protecting hands in dark environments
- **13-gauge fiberglass and polyester liner:** Sweat-proof all-day comfort
- **Ergonomic design:** Naturally curved fit, for reduced hand fatigue

Performance Standards & Regulatory Compliance



Technologies



Specifications

| BRAND STYLE | DESCRIPTION | Gauge | SIZE | LENGTH | COATING COLOR | PACKAGE |
|------------------|---|-------|-----------------|-------------------------------|---------------|-----------------------------|
| ActivArm® 97-013 | Finishing: Palm Coated Coating Material: Water-Based polyurethane and nitrile Liner Material: Fiber glass, Polyester Cuff Style: Knitwrist | 13 | 7, 8, 9, 10, 11 | 230-270 mm/ 9.05-10.63 inches | Orange | 12 pairs/bag, 6 bags/carton |

For additional information visit us at www.ansell.com, or call us at

Europe, Middle East & Africa Region

Ansell Healthcare Europe NV
 Riverside Business Park
 Blvd International, 55
 1070 Brussels, Belgium
 T: +32 (0) 2 528 74 00
 F: +32 (0) 2 528 74 01

North America Region

Ansell Healthcare Products LLC
 111 Wood Avenue South,
 Suite 900
 Iselin, NJ 08830, USA
 T: +1 800 800 0444
 F: +1 800 800 0445

Australia

Ansell Limited
 Level 3,678 Victoria Street,
 Richmond, Vic, 3121
 Australia
 T: +61 1800 337 041
 F: +61 1800 803 578

Asia Pacific Region

Ansell Global Trading Center
 (Malaysia) Sdn Bhd
 Prima 6, Prima Avenue
 Block 3512, Jaijan Teknokrat 6
 T: +603 8310 6688
 F: +603 8310 6699

Latin America & Caribbean Region

Ansell Commercial Mexico S.A. de C.V.
 Blvd. Bernardo Quintana No. 7001-C,
 Q7001 Torre II,
 Suites 1304, 1305 y 1306,
 Col. Centro Sur, c.p. 76079
 Queretaro, Qro. Mexico
 T: +52 442 248 1544 / 248 3133

Canada

Ansell Canada
 105 Lauder
 Cowansville, QC J2K 2K8
 Canada
 T: +1 800 363 8340
 F: +1 800 267 3551