



Oil



Heavy Duty

## Oil-repellent nitrile-coated work gloves, for tasks requiring durability and resistance to sharp materials

- **Enhanced flexibility and durability:** ActivArm® Hycron® 27-810 nitrile-coated gloves offer greater flexibility than PVC-coated gloves, as well as three times more durability than heavy-duty leather alternatives
- **Specialized protection:** Their unique nitrile formulation also ensures robust hand protection against sharp and abrasive materials, as well as oil and grease
- **Enhanced features:** ActivArm® Hycron® 27-810 work gloves feature a long safety cuff, further boosting hand and wrist protection
- **Reduced surface defect risks:** Silicone-free by design, they are ideal for metalworking and motor manufacture, averting any contaminant transfer to paint before painting
- **Elevated comfort:** These ActivArm® gloves' cotton jersey fabric also grants wearers optimal comfort, for less strenuous everyday hand protection



### Industries

- Automotive
- Machinery and Equipment
- Metal fabrication
- Chemical

### Applications

- Handling metal sheets & panels
- Metalworking & assembly operations
- Press injection molding
- Seizing and finishing structural parts
- Fixing, clipping parts and wire harnesses; connecting devices
- Assembly & inspection of components
- Opening furnaces draining pumps valves or lines and crackers BTX process

Key Features

- **Nitrile formulation:** Flexibility, durability, abrasion resistance\*
- **Long safety cuff:** Enhanced hand and wrist protection
- **Silicone-free design:** Assured cleanliness for metal and motor manufacture

*\*3x more durability than heavy-duty leather alternatives*

Performance Standards & Regulatory Compliance



Specifications

| BRAND   STYLE                                     | DESCRIPTION                                                                                                                                | Gauge | SIZE | LENGTH | COATING COLOR | PACKAGE                      |
|---------------------------------------------------|--------------------------------------------------------------------------------------------------------------------------------------------|-------|------|--------|---------------|------------------------------|
| ActivArmr <sup>®</sup> Hycron <sup>®</sup> 27-810 | <b>Finishing:</b> Fully Coated<br><b>Coating Material:</b> Nitrile<br><b>Liner Material:</b> Cotton<br><b>Cuff Style:</b> Long safety cuff |       | 10   | 315 mm | Blue          | 12 pairs/bag, 12 bags/carton |

For additional information visit us at [www.ansell.com](http://www.ansell.com), or call us at

Europe, Middle East & Africa Region

Ansell Healthcare Europe NV  
Riverside Business Park  
Blvd International, 55  
1070 Brussels, Belgium  
T: +32 (0) 2 528 74 00  
F: +32 (0) 2 528 74 01

Latin America & Caribbean Region

Ansell Commercial Mexico S.A. de C.V.  
Blvd. Bernardo Quintana No. 7001-C,  
Q7001 Torre II,  
Suites 1304, 1305 y 1306,  
Col. Centro Sur, c.p. 76079  
Queretaro, Qro. Mexico  
T: +52 442 248 1544 / 248 3133

North America Region

Ansell Healthcare Products LLC  
111 Wood Avenue South,  
Suite 900  
Iselin, NJ 08830, USA  
T: +1 800 800 0444  
F: +1 800 800 0445

Canada

Ansell Canada  
105 Lauder  
Cowansville, QC J2K 2K8  
Canada  
T: +1 800 363 8340  
F: +1 800 267 3551

Australia

Ansell Limited  
Level 3,678 Victoria Street,  
Richmond, Vic, 3121  
Australia  
T: +61 1800 337 041  
F: +61 1800 803 578

Asia Pacific Region

Ansell Global Trading Center  
(Malaysia) Sdn Bhd  
Prima 6, Prima Avenue  
Block 3512, Jalan Teknokrat 6  
T: +603 8310 6688  
F: +603 8310 6699