



Oil



Medium Duty

## Durable oil-repellent safety gloves, combining mechanical protection and flexibility

- **Specialized protection:** ActivArm<sup>®</sup> Hylite 47-409 industrial gloves feature a special nitrile formulation that combines oil repellency, mechanical protection, and flexibility with advanced abrasion resistance compliant with ANSI/ISEA and EN standards.
- **Elevated comfort:** With their naturally contoured design, interlock lining and generous sizing, these abrasion-resistant gloves offer the same comfort as a cotton or light leather glove, facilitating longer wear\*
- **Reduced surface defect risks:** ActivArm<sup>®</sup> Hylite 47-409 work gloves are silicone-free, ensuring sheet metal is kept clean and the risk of contaminant transfer to metal prior to painting is minimized
- **Genuine convenience:** These protective gloves are also available in a wide range of styles, lengths and sizes  
\*ActivArm<sup>®</sup> gloves outwear cotton gloves by a margin of 12 to 1, light leather gloves by a margin of 5 to 1, and 3 to 1 for PVC-coated gloves



### Industries

- Automotive
- Machinery and Equipment
- Metal fabrication

### Applications

- Handling metal sheets & panels
- Chassis assembly, body trimming
- Final assembly
- Inspection (picking, checking and marking)
- Cutting glasses, sheets, panels
- Fabricating metal parts, glass sheets
- Assembly & inspection of components

# ACTIVARMR®

PERSONAL PROTECTIVE GEAR

## 47-409

Comfortable oil-repellent glove for medium duty tasks

### Key Features

- **Special nitrile formulation:** Oil repellency and mechanical protection
- **Contoured design and interlock knit liner:** Enhanced comfort levels
- **Silicone-free design:** For metal sheet-friendly industrial work gloves

### Performance Standards & Regulatory Compliance



ANSI/ISEA 105-2024



EN388: 2016



3111A

### Specifications

BRAND   STYLE	DESCRIPTION	Gauge	SIZE	LENGTH	COATING COLOR	PACKAGE
ActivArm <sup>®</sup> Hylite™ 47-409	<b>Finishing:</b> Fully Coated <b>Coating Material:</b> Nitrile <b>Liner Material:</b> Interlock cotton <b>Cuff Style:</b> Nitragold™		7, 8, 9, 10	273-289 mm; 10.74-11.37 inches	Blue	12 pairs/bag, 12 bags/carton

### For additional information visit us at [www.ansell.com](http://www.ansell.com), or call us at

#### Europe, Middle East & Africa Region

Ansell Healthcare Europe NV  
Riverside Business Park  
Blvd International, 55  
1070 Brussels, Belgium  
T: +32 (0) 2 528 74 00  
F: +32 (0) 2 528 74 01

#### North America Region

Ansell Healthcare Products LLC  
111 Wood Avenue South,  
Suite 900  
Iselin, NJ 08830, USA  
T: +1 800 800 0444  
F: +1 800 800 0445

#### Australia

Ansell Limited  
Level 3, 678 Victoria Street,  
Richmond, Vic, 3121  
Australia  
T: +61 1800 337 041  
F: +61 1800 803 578

#### Asia Pacific Region

Ansell Global Trading Center  
(Malaysia) Sdn Bhd  
Prima 6, Prima Avenue  
Block 3512, Jaijan Teknokrat 6  
T: +603 8310 6688  
F: +603 8310 6699

#### Latin America & Caribbean Region

Ansell Commercial Mexico S.A. de C.V.  
Blvd. Bernardo Quintana No. 7001-C,  
Q7001 Torre II,  
Suites 1304, 1305 y 1306,  
Col. Centro Sur, c.p. 76079  
Queretaro, Qro. Mexico  
T: +52 442 248 1544 / 248 3133

#### Canada

Ansell Canada  
105 Lauder  
Cowansville, QC J2K 2K8  
Canada  
T: +1 800 363 8340  
F: +1 800 267 3551

Ansell, ® and ™ are trademarks owned by Ansell Limited or one of its affiliates. US Patented and US and non-US Patents Pending: [www.ansell.com/patentmarking](http://www.ansell.com/patentmarking) © 2025 Ansell Limited. All Rights Reserved.

Neither this document nor any other statement made herein by or on behalf of Ansell should be construed as a warranty of merchantability or that any Ansell product is fit for a particular purpose. Ansell assumes no responsibility for the suitability or adequacy of an end user's selection of gloves for a specific application.

