

Silicone clearview autoclavable goggles with anti-fog properties

- **Elevated comfort:** These BioClean™ clearview goggles feature a non-linting, latex-free headband with a super-soft lightweight silicone rubber frame that enables prolonged use & user comfort
- **Advanced defenses:** BioClean™ Clearview Autoclavable Goggles BCAH possess an indirect ventilation system that helps reduce the risk of contamination entering the controlled environment
- **Maximized view:** These BioClean™ clearview goggles provide wearers an optically correct, toughened polycarbonate and anti-fog lens, making them ideal for use over eyeglasses
- **Improved durability:** These autoclavable cleanroom goggles can tolerate up to 1 gamma irradiation cycles and are tested to withstand 40 autoclave cycles for housing of 30 minutes duration at 121°C/250°F. Anti-fog performance remaining for up to 25 autoclave cycles for lens (anti-fogging) with no signs of degradation (under laboratory conditions)



Key Features and Benefits

- **Lightweight material:** Enables prolonged use and user comfort
- **Indirect ventilation system:** Lowers the risk of contamination
- **Anti-fog properties:** For unobstructed vision

Industries

- Controlled and Critical Environments
- Laboratory and Research
- Production and Manufacturing

Recommended For

- Medical Device Manufacturing
- Organic and material synthesis
- Preparing pharmaceutical products
- Clean room cleaning and preparing
- Nutraceutical manufacturing
- Semiconductor manufacturing
- White goods assembly



BioClean™ Clearview Autoclavable Goggles BCAH

TECHNICAL DATA SHEET

PRODUCT INFORMATION

Material	Polycarbonate, Silicone rubber, Polypropylene
Color	White
Audit Standards	Manufacturing QMS Audit Standards ISO 9001
Standards	CE Number, EN 166:2001, Category II, UKCA
Packaging Overview	Goggle (BCAH): One piece per sealed PE bag (to be removed prior to autoclaving); 12 bags per inner box; five boxes per carton (60 pieces) Replacement Lens (BCAH-SL): One piece per sealed PE bag; 10 bags per inner box; 10 boxes per carton (100 pieces) Replacement Strap (BCAH-SS): 25 pieces per sealed PE bag; two bags per inner box; 10 boxes per carton (500 pieces)
Country Of Origin	Malaysia
Sterilization Method	Supplied non-sterile. To be autoclaved at 121°C/250°F for 30 minutes.
Cleanroom Class	Class 10/ISO 4 & EU GMP Grade A
Shelf Life	Five (5) years from date of manufacture.
Optical Class	1
Storage Instructions	Keep away from direct sunlight; store in a dry place and keep in the original packaging. Keep away from ozone sources. If products are properly stored, as indicated, they won't lose their performances or change characteristics significantly. If products could be affected by ageing or storage, the expiry date is mentioned on the packaging materials.
Weight	106g

PHYSICAL PROPERTIES

Overall Dimensions	Total Weight (± 2g) 106g Lens Thickness (± 0.3mm) 1mm Bridge Width (± 0.5mm) 50mm Bridge Height(±0.5mm)20mm Overall Width (hinge to hinge)(±3mm) 180mm Overall Height (± 3mm) 92mm
---------------------------	--

ORDERING INFORMATION

	SIZE	Autoclavable Goggles	Replacement Lens	Replacement Strap
BCAH	REORDER NO.	BCAH	BCAH-SL	BCAH-SS



BioClean™ Clearview Autoclavable Goggles BCAH

EXPLANATION OF FRAME MARKINGS

Required Markings	Markings On Frame	Meaning
Manufacturers Identification Mark	Ansell	Ansell
Brand	BioClean™	BioClean™
Field of Use	3	Liquids (droplets or splashes)
Field of Use	BT	Medium energy impact at extremes of temperature
Conformity Mark	CE	Conformity with European Standards
Field of Use	UKCA	Conformity with Great Britain Standard

EXPLANATION OF OCULAR MARKINGS

Required Markings	Markings On Ocular	Meaning
Manufacturers Identification Mark	BioClean	BioClean™
Optical Class	1	High optical quality
Mechanical Strength	BT	Medium energy impact at extremes of temperature
Field of Use	N	Resistance to fogging
Field of Use	O	Original ocular
Original Or Replacement Ocular	∇	Replacement ocular

For additional information visit us at www.ansell.com, or call us at

Europe, Middle East & Africa Region

Ansell Healthcare Europe NV
T: +32 (0) 2 528 74 00
F: +32 (0) 2 528 74 01

Asia Pacific Region

Ansell Global Trading Center
T: +603 8310 6688
F: +603 8310 6699

North America Region

Ansell Healthcare Products LLC
US T: +1 800 800 0444
US F: +1 800 800 0445
CA T: +1-800-363-8340

Latin America & Caribbean Region

Ansell Commercial Mexico S.A. de C.V.
T: +52 442 248 1544 / 248 3133

Australia

Ansell Limited
T: +61 1800 337 041
F: +61 1800 803 578

UK

Ansell Nitritex
T: +44 1638 663338
F: +44 1638 668890

Performance Standards and
Regulatory Compliance



Ansell, ® and ™ are trademarks owned by Ansell Limited or one of its affiliates. US Patented and US and non-US Patents Pending: www.ansell.com/patentmarking © 2024 Ansell Limited. All Rights Reserved.

Neither this document nor any other statement made herein by or on behalf of Ansell should be construed as a warranty of merchantability or that any Ansell product is fit for a particular purpose. Ansell assumes no responsibility for the suitability or adequacy of an end user's selection of gloves for a specific application.

