

# Sterile glove liners that offer comfort, dexterity and heightened cut resistance

- **Advanced defenses:** The BioClean™ Cut Resistant Liner S-BCRL features innovative Dyneema® Diamond yarn, resulting in heightened cut resistance
- **Specialized protection:** These glove liners comply with ANSI/ISEA 105-2024 CUT A2 and EN ISO B standards, ensuring safe handling of sharp objects.
- **Sterility assurance:** These ambidextrous glove liners also boast an SAL (Sterility Assurance Level) of  $10^{-6}$ , for reduced contamination risks
- **Improved fit:** The BioClean™ Cut Resistant Liner S-BCRL are specially designed to be worn between two cleanroom gloves



## KEY FEATURES & BENEFITS

- **Dyneema® Diamond yarn:** For glove liners with robust cut protection
- **Compliant with ANSI/ISEA 105-2024 CUT A2 and EN ISO B standards:** ensuring safe handling of sharp objects.
- **SAL (Sterility Assurance Level) of  $10^{-6}$ :** Reduced contamination risks

WARNING: No liner provides complete protection against cuts. Use care when handling sharp objects.

## Industries

- Controlled and Critical Environments
- Laboratory and Research
- Production and Manufacturing
- Lab and R&D
- Sterile Processing Department



## S-BCRL

Sterile Cut Resistance Cleanroom Liner

### TECHNICAL DATA SHEET

	Product Information
Color	Yellow, Green, Orange, Blue, Red
Shape	Ambidextrous
Regulatory/Standard Compliance	ANSI/ISEA 105-2024, EN 420:2003 + A1:2009, EN 388:2016, ISO 11137-1:2006, Category II
Packaging	One pair per inner PE wallet; one wallet per sealed EasyTear PE pouch; 10 pouches per sealed outer PE bag; 10 outer bags per lined carton (100 pairs).
Country of Origin	Sri Lanka
Available sizes	XS (5.5 - 6), S (6.5 - 7), M (7.5 - 8), L (8.5 - 9), XL (9.5 - 10)
Sterilization Method	GAMMA irradiation (25 kGy)
Sterilization Minimum Dose	25kGy
Sterility Assurance Level	10 <sup>-6</sup>
Cleanroom Class	Class 10/ISO Class 4 & EU GMP Grade A/B and other sterile cleanrooms
Shelf Life	Five (5) years from date of manufacture.



# S-BCRL

## Sterile Cut Resistance Cleanroom Liner

Physical Properties						Testing Method
Sizes	XS (5.5 - 6)	S (6.5 - 7)	M (7.5 - 8)	L (8.5 - 9)	XL (9.5 - 10)	EN 420
Typical Length (mm/in)	XS-162/6.3, S-174/6.8, M-182/7.1, L-192/7.5, XL- 202/7.9					
Palm Width (mm/in)	70/2.7	72/2.8	75/2.9	79/3.1	85/3.3	

### ORDERING INFORMATION

SIZE	XS (5.5 - 6)	S (6.5 - 7)	M (7.5 - 8)	L (8.5 - 9)	XL (9.5 - 10)
REORDER NO.	S-BCRL-5055	S-BCRL-6065	S-BCRL-7075	S-BCRL-8085	S-BCRL-9090

### PERFORMANCE STANDARDS AND REGULATORY COMPLIANCE



For additional information visit us at [www.ansell.com](http://www.ansell.com), or call us at

#### Europe, Middle East & Africa Region

Ansell Healthcare Europe NV  
T: +32 (0) 2 528 74 00  
F: +32 (0) 2 528 74 01

#### Asia Pacific Region

Ansell Global Trading Center  
T: +603 8310 6688  
F: +603 8310 6699

#### North America Region

Ansell Healthcare Products LLC  
US T: +1 800 800 0444  
US F: +1 800 800 0445  
CA T: +1-800-363-8340

#### Latin America & Caribbean Region

Ansell Commercial Mexico S.A. de C.V.  
T: +52 442 248 1544 / 248 3133

#### Australia

Ansell Limited  
T: +61 1800 337 041  
F: +61 1800 803 578

#### UK

Ansell Nitritex  
T: +44 1638 663338  
F: +44 1638 668890

Ansell, ® and ™ are trademarks owned by Ansell Limited or one of its affiliates. US Patented and US and non-US Patents Pending: [www.ansell.com/patentmarking](http://www.ansell.com/patentmarking) © 2024 Ansell Limited. All Rights Reserved.

Neither this document nor any other statement made herein by or on behalf of Ansell should be construed as a warranty of merchantability or that any Ansell product is fit for a particular purpose. Ansell assumes no responsibility for the suitability or adequacy of an end user's selection of gloves for a specific application.

