

EPDM RABS/isolator gloves, manufactured with premium FDA-approved material, for fewer glove changes

Port size: 254mm/10"
Thickness: 0.6mm/24 mil

- **Optimized durability:** The AlphaTec® EPDM Isolator Glove 85-503 is designed for repeated autoclave sterilization (up to 50 times), resulting in fewer replacements
- **Assured protection:** These isolator gloves satisfy EN ISO 374 chemical resistance standards, for assured protection from hydrogen peroxide and common disinfecting chemicals
- **Increased eco-friendliness:** The AlphaTec® EPDM Isolator Glove 85-503 is halogen-free, making it safe for disposal by incineration
- **Food handling compliance:** These EPDM gloves adhere to FDA Food Contact regulation 21 CFR 177 (FDA Positive List) for Indirect Food Additives



KEY FEATURES & BENEFITS

- **EPDM composition:** Suitable for repeated autoclave sterilization
- **Chemical resistance:** Hydrogen peroxide/common disinfecting chemicals
- **FDA food handling compliance:** For safe, dependable isolator gloves

TECHNICAL DATA SHEET

| | |
|--|--|
| Product Reference | 85-503 |
| Material | Ethylene propylene diene rubber_EPDM |
| Color | Black |
| Shape | Ambidextrous |
| External Glove Surface | Smooth |
| Cuff Style | Beaded |
| Storage Instructions | Store in a dry and dark environment, temperature of 5°C to 22°C. Retain in original packaging when not in use. |
| Available Sizes | 11, 9.5 |
| Temperature Range | From -20°C to 130°C |
| Cleanroom Class | Non-Critical Environment |
| Shelf Life | Three (3) years from date of manufacture. |
| Tested For Use With Chemotherapy Drugs | No |
| Standards | CE 0493, EN 388:2016, EN ISO 21420:2020, EN ISO 374-1:2016 Type B, EN ISO 374-5:2016, EN ISO 374-5:2016, EN 420:2003 + A1:2009, Category III |
| Vulcanization Chemical Accelerators | <ul style="list-style-type: none">• Diphenyl guanidine• Tetramethylthiuram disulfide |

PHYSICAL PROPERTIES

| | Typical Values | Testing Method |
|--|------------------|----------------|
| Typical Length (mm/in) | 800/32 | EN ISO 21420 |
| Port Size | 10" | |
| Target Single Wall Palm Thickness (mm/mil) | 0.60 mm / 24 mil | EN 455-2 |
| Target Single Wall Finger Thickness (mm/mil) | 0.60 mm / 24 mil | EN 455-2 |
| Target Single Wall Cuff Thickness (mm/mil) | 0.60 mm / 24 mil | EN 455-2 |

PROTECTION AGAINST MECHANICAL RISKS, EN 388:2016+A1:2018

| Risk | Performance level |
|----------------------|-------------------|
| Abrasion Resistance | Level 2 |
| Blade Cut Resistance | Level 1 |
| Tear Resistance | Level 1 |
| Puncture Resistance | Level 1 |

ORDERING INFORMATION

| | PORT SIZE | 10"/254mm | 10"/254mm |
|--------|-------------|-----------|-----------|
| | SIZE | 9.5 | 11 |
| 85-503 | REORDER NO. | 85503095 | 85503110 |

For additional information visit us at www.ansell.com, or call us at

Europe, Middle East & Africa Region

Ansell Healthcare Europe NV
T: +32 (0) 2 528 74 00
F: +32 (0) 2 528 74 01

Asia Pacific Region

Ansell Global Trading Center
T: +603 8310 6688
F: +603 8310 6699

North America Region

Ansell Healthcare Products LLC
US T: +1 800 800 0444
US F: +1 800 800 0445
CA T: +1-800-363-8340

Latin America & Caribbean Region

Ansell Commercial Mexico S.A. de C.V.
T: +52 442 248 1544 / 248 3133


Australia

Ansell Limited
T: +61 1800 337 041
F: +61 1800 803 578

UK

Ansell Nitritex
T: +44 1638 663338
F: +44 1638 668890

Performance Standards and Regulatory Compliance



Ansell, ® and ™ are trademarks owned by Ansell Limited or one of its affiliates. US Patented and US and non-US Patents Pending: www.ansell.com/patentmarking © 2024 Ansell Limited. All Rights Reserved.

Neither this document nor any other statement made herein by or on behalf of Ansell should be construed as a warranty of merchantability or that any Ansell product is fit for a particular purpose. Ansell assumes no responsibility for the suitability or adequacy of an end user's selection of gloves for a specific application.