


## Extra-long disposable gloves for superior product and worker protection

- **Extended chemical protection:** MICROFLEX<sup>®</sup> 93-243 gloves feature an extra-long cuff to shield more of your arm and provide excellent chemical splash protection — ideal for laboratory and pharmaceutical manufacturing, as well as food processing workers
- **Reduced allergy risk:** Manufactured without accelerators, helping to protect users from Type IV skin allergies
- **Ultra-long cuff design:** MICROFLEX<sup>®</sup> 93-243 gloves feature an elbow-length cuff designed to prevent roll-down and minimize the risk of cross-contamination
- **Secure grip:** The textured palm and fingers of these gloves results in a more confident, secure grip of instruments and glassware
- **Product protection:** To prevent contamination and protect product integrity, these gloves are packed in polybags



### Industries

- Food Processing
- Life Sciences

### Recommended For

- Enhanced tactile sensitivity and dexterity, especially for delicate procedures

# TECHNICAL DATA SHEET

Product Information	
External Glove Surface	Fully Textured
Audit Standards	ISO 9001
Product Certification	Personal Protective Equipment Regulation (EU) 2016/425 Category III risks
Packaging Overview	100 gloves per polybag 10 polybags per case 1000 gloves per case
Storage Instructions	Keep out of direct sunlight; store in a cool and dry place. Keep away from sources of ozone or ignition.
Country Of Origin	Malaysia
Product Segmentation	High Risk
Antistatic	Yes EN1149
Silicone Free	Yes
Vulcanization Chemical Accelerators	<ul style="list-style-type: none"> <li>Made without accelerators</li> </ul> <p><i>Only a very small number of users may be sensitive to this ingredient(s) and hence may develop irritant and/or allergic contact reactions.</i></p>

## PHYSICAL PROPERTIES

	Typical Values		Testing Method
Length (mm/inches)	395 / 15.6		ASTM D3767,EN 420
Freedom from Holes (Inspection level I)	1.5 AQL		ASTM D5151,EN 455-1
Palm Thickness (mm/mils)	0.13 / 5.1		ASTM D3767,EN 420
Finger Thickness (mm/mils)	0.17 / 6.7		ASTM D3767,EN 420
	<b>BEFORE AGING</b>	<b>AFTER AGING</b>	
Ultimate Tensile Strength (MPa)	≥ 14	≥ 14	ASTM D412 & D573
Elongation at Break (%)	≥ 500	≥ 400	ASTM D412
Force at break (N)	≥ 6	≥ 6	

## ORDERING INFORMATION

Size	XS (5.5 - 6)	S (6.5 - 7)	M (7.5 - 8)	L (8.5 - 9)	XL (9.5 - 10)	XXL (10.5 - 11)
Product Code	93243060	93243070	93243080	93243090	93243100	93243110

## Performance Standards and Regulatory Compliance



## For additional information visit us at [www.ansell.com](http://www.ansell.com), or call us at

### Europe, Middle East & Africa Region

Ansell Healthcare Europe NV  
T: +32 (0) 2 528 74 00  
F: +32 (0) 2 528 74 01

### Asia Pacific Region

MY +603 8310 6688  
apac.medical@ansell.com  
CN: +86 21 38275000  
infochina@ansell.com  
JP: +813 5549 8151  
info.medical.jp@ansell.com

### North America Region

Ansell Healthcare Products LLC  
T: +1 800 800 0444  
F: +1 800 800 0445

### Latin America & Caribbean Region

BR +55 (11) 3356-3100  
latam.medical@ansell.com  
MX: +52 442 296 2050  
latam.medical@ansell.com  
CO: +57 1 288 3247  
latam.medical@ansell.com

### Australia

Ansell Limited  
T: +61 1800 337 041  
F: +61 1800 803 578

### Russia

Ansell PYC  
Ten. +7 495 258 13 16

Ansell, ® and ™ are trademarks owned by Ansell Limited or one of its affiliates. US Patented and US and non-US Patents Pending; [www.ansell.com/patentmarking](http://www.ansell.com/patentmarking) © 2024 Ansell Limited. All Rights Reserved.

Neither this document nor any other statement made herein by or on behalf of Ansell should be construed as a warranty of merchantability or that any Ansell product is fit for a particular purpose. Ansell assumes no responsibility for the suitability or adequacy of an end user's selection of gloves for a specific application.

