

# ACTIVARMR®

PERSONAL PROTECTIVE GEAR

## Electrical Protection Class 0 - RIG011Y

Flexible and durable electrical safety gloves,  
protecting workers with fitted comfort

Previously known as: E014Y



Electrical



Light Duty

## Flexible and durable electrical safety gloves, protecting workers\* with fitted comfort

- **Heightened durability and flexibility:** Made from natural rubber latex, using an eco-conscious dipping process, ActivArm<sup>®</sup> Electrical Protection Class 0 - RIG011Y electrical gloves are both flexible and durable
- **Advanced ergonomics:** These insulated gloves' non-splayed fingers and hand-at-rest shape lessen hand fatigue
- **Elevated comfort:** A flared cuff ensures ventilation and room for clothing
- **Increased practicality:** These electrical safety gloves' smooth finish make donning and doffing easy
- **Specialized defenses:** They are arc flash certified\*, withstand a touch voltage AC maximum of 1000 V (DC maximum 1500) and tolerate acid, ozone and very low temperatures\*\*
- **Certified protection:** They also meet relevant NFPA, OSHA and CSA standards  
\*APC 1 in combination with 96-002 leather protectors  
\*\*Category A, Z and C



ARC FLASH  
RESISTANT

### Industries

- Automotive
- Electrical
- Construction
- Mining
- Machinery and Equipment

### Applications

- Applications with risk of touch voltage
- Electrical Contractors
- Hybrid engine manufacturing and repair
- Maintenance Repairs and Operations in all industrial environments (MRO)
- Mass Transit Repair and Maintenance
- Power maintenance, repair & transmission
- Telecom repair near electrical wires

# ACTIVARMR®

PERSONAL PROTECTIVE GEAR

## Electrical Protection Class 0 - RIG011Y

Flexible and durable electrical safety gloves,  
protecting workers with fitted comfort

Previously known as: E014Y

### Key Features

- **Natural rubber latex formulation:** Inherent durability and flexibility
- **Ergonomic design:** Lesser hand fatigue, greater comfort
- **Generous flared cuff:** Adequate space for both clothing and ventilation  
\*Arc flash certified as per IEC 614821-2:2014 and ATSM F2675:2021 standards

### Performance Standards & Regulatory Compliance



### Specifications

BRAND   STYLE	DESCRIPTION	Gauge	SIZE	LENGTH	COATING COLOR	PACKAGE
ActivArmr Electrical Protection Class 0 - RIG011Y	<b>Coating Material:</b> Natural Latex Rubber <b>Cuff Style:</b> Straight Cuff with rolled beaded edge		7, 8, 8.5, 9, 9.5, 10, 10.5, 11, 12	280mm/11inch	Yellow	1 pair/pack, 10 pairs/carton

For additional information visit us at [www.ansell.com](http://www.ansell.com), or call us at

#### Europe, Middle East & Africa Region

Ansell Healthcare Europe NV  
Riverside Business Park  
Blvd International, 55  
1070 Brussels, Belgium  
T: +32 (0) 2 528 74 00  
F: +32 (0) 2 528 74 01

#### Latin America & Caribbean Region

Ansell Commercial Mexico S.A. de C.V.  
Blvd. Bernardo Quintana No. 7001-C,  
Q7001 Torre II,  
Suites 1304, 1305 y 1306.  
Col. Centro Sur, c.p. 76079  
Querétaro, Qro. Mexico  
T: +52 442 248 1544 / 248 3133

#### North America Region

Ansell Healthcare Products LLC  
111 Wood Avenue South,  
Suite 900  
Iselin, NJ 08830, USA  
T: +1 800 800 0444  
F: +1 800 800 0445

#### Canada

Ansell Canada  
105 Launder  
Cowansville, QC J2K 2K8  
Canada  
T: +1 800 363 8340  
F: +1 800 267 3551

#### Australia

Ansell Limited  
Level 3,678 Victoria Street,  
Richmond, Vic, 3121  
Australia  
T: +61 1800 337 041  
F: +61 1800 803 578

#### Asia Pacific Region

Ansell Global Trading Center  
(Malaysia) Sdn Bhd  
Prima 6, Prima Avenue  
Block 3512, Jalan Teknokrat 6  
T: +603 8310 6688  
F: +603 8310 6699