

## Clearview autoclavable goggles, featuring an anti-scratch, optically correct lens

- **Increased comfort:** BioClean™ Clearview Autoclavable Goggles BCAG are designed with a non-linting latex-free headband and a soft thermoplastic rubber frame ideal for use over eyeglasses
- **Reduced contamination risks:** BioClean™ Clearview goggles feature upper vents with an indirect lower ventilation system to minimize the risks of contamination when entering controlled environments
- **Enhanced features:** These autoclavable goggles feature a toughened polycarbonate, optically correct lens with anti-scratch and anti-fog performance for up to 25 cycles without degradation, ensuring clear vision for wearers
- **Improved durability:** They are also tested to withstand 40 autoclave cycles of 30 minutes duration at 121°C/250°F



### Key Features and Benefits

- **Thermoplastic rubber frame:** For better fit and wearer comfort
- **Indirect ventilation system:** Reduced risks of contamination
- **Sturdy, polycarbonate lens:** Prevents scratches, ensures a clear vision

### Industries

- Controlled and Critical Environments
- Laboratory and Research
- Production and Manufacturing

### Recommended For

- Medical Device Manufacturing
- Biotechnologies Blending operations
- Handling active material  
Maintaining equipment and instruments
- Organic and material synthesis
- Preparing pharmaceutical products
- Clean room cleaning and preparing
- Nutraceutical manufacturing
- Semiconductor manufacturing
- White goods assembly



# BioClean™ Clearview Autoclavable Goggles BCAG

## TECHNICAL DATA SHEET

### PRODUCT INFORMATION

<b>Material</b>	Thermoplastic rubber, Polycarbonate, Polypropylene, Silicone
<b>Color</b>	White
<b>Audit Standards</b>	Manufacturing QMS Audit Standards ISO 9001
<b>Standards</b>	EN 166:2001, Category II
<b>Packaging Overview</b>	Goggle (BCAG): One piece per sealed PE bag ; 12 bags per inner box; five boxes per carton (60 pieces) Replacement Lens (BCAG-SL): One piece per sealed PE bag; 10 bags per inner box; 10 boxes per carton (100 pieces) Replacement Strap (BCAG-SS)*: 25 pieces per sealed PE bag; two bags per inner box; 10 boxes per carton (500 pieces)  *Strap only, without adjuster hook and strap clip.
<b>Country Of Origin</b>	Taiwan
<b>Sterilization Method</b>	Supplied non-sterile. To be autoclaved at 121°C/250°F for 30 minutes
<b>Cleanroom Class</b>	Class 10/ISO 4 & EU GMP Grade A
<b>Shelf Life</b>	Five (5) years from date of manufacture.
<b>Classification</b>	EN166
<b>Optical Class</b>	1
<b>Storage Instructions</b>	Store in a dry, cool place (<40°C) away from direct sunlight and fluorescent light.
<b>Weight</b>	103g

### PHYSICAL PROPERTIES

<b>Overall Dimensions</b>	Lens Thickness ( $\pm 0.3\text{mm}$ ): 3.1mm Bridge Width ( $\pm 0.5\text{mm}$ ): 70mm Bridge Height ( $\pm 0.5\text{mm}$ ): 26mm Overall Width (hinge to hinge)( $\pm 3\text{mm}$ ): 190mm Overall Height ( $\pm 3\text{mm}$ ): 85mm
---------------------------	---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------

### ORDERING INFORMATION

	SIZE	Autoclavable Goggles	Replacement Lens	Replacement Strap
BCAG	REORDER NO.	BCAG	BCAG-SL	BCAG-SS



# BioClean™ Clearview Autoclavable Goggles BCAG

## EXPLANATION OF FRAME MARKINGS

Required Markings	Markings On Frame	Meaning
Manufacturers Identification Mark	Ansell	Ansell
Brand	BioClean™	BioClean™
Standard Number	EN166	European Standard on Personal Eye Protection
Field of Use	BT	Medium energy impact at extremes of temperature
Conformity Mark	CE	Conformity with European Standards
Field of Use	UKCA	Conformity with Great Britain Standard

## EXPLANATION OF OCULAR MARKINGS

Required Markings	Markings On Ocular	Meaning
Manufacturers Identification Mark	BioClean™	BioClean™
Optical Class	1	High optical quality
Mechanical Strength	BT	Medium energy impact at extremes of temperature
Field of Use	N	Resistance to fogging
Field of Use	O	Original Ocular
Original Or Replacement Ocular	∇	Replacement Ocular

For additional information visit us at [www.ansell.com](http://www.ansell.com), or call us at

### Europe, Middle East & Africa Region

Ansell Healthcare Europe NV  
T: +32 (0) 2 528 74 00  
F: +32 (0) 2 528 74 01

### Asia Pacific Region

Ansell Global Trading Center  
T: +603 8310 6688  
F: +603 8310 6699

### North America Region

Ansell Healthcare Products LLC  
US T: +1 800 800 0444  
US F: +1 800 800 0445  
CA T: +1-800-363-8340

### Latin America & Caribbean Region

Ansell Commercial Mexico S.A. de C.V.  
T: +52 442 248 1544 / 248 3133

### Australia

Ansell Limited  
T: +61 1800 337 041  
F: +61 1800 803 578

### UK

Ansell Nitritex  
T: +44 1638 663338  
F: +44 1638 668890

Ansell, ® and ™ are trademarks owned by Ansell Limited or one of its affiliates. US Patented and US and non-US Patents Pending: [www.ansell.com/patentmarking](http://www.ansell.com/patentmarking) © 2024 Ansell Limited. All Rights Reserved.

Neither this document nor any other statement made herein by or on behalf of Ansell should be construed as a warranty of merchantability or that any Ansell product is fit for a particular purpose. Ansell assumes no responsibility for the suitability or adequacy of an end user's selection of gloves for a specific application.

