

## Silicone clearview autoclavable goggles with anti-scratch and anti-fog properties

- **Elevated comfort:** These BioClean™ clearview goggles feature a non-linting, latex-free headband with a super-soft lightweight silicone rubber frame that enables prolonged use and user comfort
- **Advanced defenses:** BioClean™ Clearview Autoclavable Goggles BCAH possess an indirect ventilation system that helps reduce the risk of contamination entering the controlled environment
- **Maximized view:** These BioClean™ clearview goggles provide wearers an optically correct, toughened polycarbonate anti-scratch and anti-fog lens, making them ideal for use over eyeglasses
- **Improved durability:** These autoclavable cleanroom goggles can tolerate up to 1 gamma irradiation cycles and are tested to withstand 40 autoclave cycles of 30 minutes duration at 121°C/250°F. Anti-fog performance remaining for up to 25 cycles with no signs of degradation (under laboratory conditions)



### Key Features and Benefits

- **Lightweight material:** Enables prolonged use and user comfort
- **Indirect ventilation system:** Lowers the risk of contamination
- **Anti-scratch, anti-fog properties:** For unobstructed vision

### Industries

- Controlled and Critical Environments
- Laboratory and Research
- Production and Manufacturing

### Recommended For

- Medical Device Manufacturing
- Biotechnologies Blending operations
- Handling active material
- Maintaining equipment and instruments
- Organic and material synthesis
- Preparing pharmaceutical products

- Clean room cleaning and preparing
- Nutraceutical manufacturing



# BioClean™ Clearview Autoclavable Goggles BCAH

## TECHNICAL DATA SHEET

### PRODUCT INFORMATION

<b>Material</b>	Polycarbonate, Silicone rubber, Polypropylene
<b>Color</b>	White
<b>Audit Standards</b>	Manufacturing QMS Audit Standards ISO 9001
<b>Standards</b>	CE Number, EN 166:2001, UKCA
<b>Packaging Overview</b>	Goggle (BCAH): One piece per sealed PE bag (to be removed prior to autoclaving); 12 bags per inner box; five boxes per carton (60 pieces) Replacement Lens (BCAH-SL): One piece per sealed PE bag; 10 bags per inner box; 10 boxes per carton (100 pieces) Replacement Strap (BCAH-SS): 25 pieces per sealed PE bag; two bags per inner box; 10 boxes per carton (500 pieces)
<b>Country Of Origin</b>	Malaysia
<b>Sterilization Method</b>	Supplied non-sterile. To be autoclaved at 121°C/250°F for 30 minutes.
<b>Cleanroom Class</b>	Class 10/ISO 4 & EU GMP Grade A
<b>Shelf Life</b>	Five (5) years from date of manufacture.
<b>Optical Class</b>	1
<b>Storage Instructions</b>	Store in a dry, cool place (<40°C) away from direct sunlight and fluorescent light.
<b>Weight</b>	106g

### PHYSICAL PROPERTIES

<b>Overall Dimensions</b>	Total Weight (± 2g) 106g Lens Thickness (± 0.3mm) 1mm Bridge Width (± 0.5mm) 50mm Bridge Height(±0.5mm)20mm Overall Width (hinge to hinge)(±3mm) 180mm Overall Height (± 3mm) 92mm
---------------------------	--

### ORDERING INFORMATION

	SIZE	Autoclavable Goggles	Replacement Lens	Replacement Strap
BCAH	REORDER NO.	BCAH	BCAH-SL	BCAH-SS



# BioClean™ Clearview Autoclavable Goggles BCAH

## EXPLANATION OF FRAME MARKINGS

Required Markings	Markings On Frame	Meaning
Manufacturers Identification Mark	Ansell	Ansell
Brand	BioClean™	BioClean™
Field of Use	3	Liquids (droplets or splashes)
Field of Use	BT	Medium energy impact at extremes of temperature
Conformity Mark	CE	Conformity with European Standards
Field of Use	UKCA	Conformity with Great Britain Standard

## EXPLANATION OF OCULAR MARKINGS

Required Markings	Markings On Ocular	Meaning
Manufacturers Identification Mark	BioClean	BioClean™
Optical Class	1	High optical quality
Mechanical Strength	BT	Medium energy impact at extremes of temperature
Field of Use	N	Resistance to fogging
Field of Use	O	Original ocular
Original Or Replacement Ocular	∇	Replacement ocular

For additional information visit us at [www.ansell.com](http://www.ansell.com), or call us at

### Europe, Middle East & Africa Region

Ansell Healthcare Europe NV  
T: +32 (0) 2 528 74 00  
F: +32 (0) 2 528 74 01

### Asia Pacific Region

Ansell Global Trading Center  
T: +603 8310 6688  
F: +603 8310 6699

### North America Region

Ansell Healthcare Products LLC  
US T: +1 800 800 0444  
US F: +1 800 800 0445  
CA T: +1-800-363-8340

### Latin America & Caribbean Region

Ansell Commercial Mexico S.A. de C.V.  
T: +52 442 248 1544 / 248 3133

### Australia

Ansell Limited  
T: +61 1800 337 041  
F: +61 1800 803 578

### UK

Ansell Nitritex  
T: +44 1638 663338  
F: +44 1638 668890

Performance Standards and  
Regulatory Compliance



Ansell, ® and ™ are trademarks owned by Ansell Limited or one of its affiliates. US Patented and US and non-US Patents Pending; [www.ansell.com/patentmarking](http://www.ansell.com/patentmarking) © 2024 Ansell Limited. All Rights Reserved.

Neither this document nor any other statement made herein by or on behalf of Ansell should be construed as a warranty of merchantability or that any Ansell product is fit for a particular purpose. Ansell assumes no responsibility for the suitability or adequacy of an end user's selection of gloves for a specific application.



