



Cut



Medium Duty

## Mechanical protection gloves granting superior cut resistance and optimal comfort

- **Heightened defenses:** HyFlex® 11-645 protective gloves leverage INTERCEPT™ Cut Resistance Technology to deliver 2x greater cut resistance\*
- **Elevated comfort:** These cut-resistant gloves provide the fit and feel of lighter protection levels while meeting ANSI/ISEA 105-2024 CUT A4 and EN ISO D safety standards
- **Improved durability:** Owing to their skin-friendly PU coating\*\*, these hand protection gloves afford superb durability for dry and slightly oily applications
- **Added feature:** In addition, these HyFlex® gloves allow wearer to use multiple touchscreen devices without having to remove their gloves
- **Reduced contamination risk:** As these industrial gloves are silicone-free, they prevent contaminant transfer to metal before painting
- **Guaranteed skin-friendliness:** HyFlex® 11-645 polyurethane gloves also possess Dermatest® and Oekotex certification



*\*Versus similar gloves made of standard HPPE yarn*

*\*\*Low DMF content <100ppm compared to industry standard <1000ppm*

### Industries

- Automotive
- Machinery and Equipment
- Metal fabrication

### Applications

- Assembly of sharp parts
- Handling metal sheets & panels
- Maintenance
- Inspection (picking, checking and marking)

# HyFlex®

ADVANCED MECHANICAL PROTECTION

## 11-645

Trusted comfort with 2x more cut resistance\*

### Key Features

- **INTERCEPT™ Cut Resistance Technology:** Twice the cut resistance\*
- **Fit and feel of an ANSI/ISEA 105-2024 CUT A2 and EN ISO B glove:** Enhanced comfort
- **PU coating\*\*:** High durability for dry and slightly oily applications

\*Versus similar gloves made of standard HPPE yarn

\*\*Low DMF content <100ppm compared to industry standard <1000ppm

### Performance Standards & Regulatory Compliance

ANSI/ISEA 105-2024



EN388: 2016



4X43D



### Technologies



**INTERCEPT™**  
Cut Resistance Technology



Touchscreen Compatible

### Specifications

BRAND   STYLE	DESCRIPTION	Gauge	SIZE	LENGTH	COATING COLOR	PACKAGE
HyFlex® 11-645	<b>Finishing:</b> Palm Coated <b>Coating Material:</b> Low DMF polyurethane <b>Liner Material:</b> Ansell INTERCEPT™ Technology <b>Cuff Style:</b> Knitwrist	13	5, 6, 7, 8, 9, 10, 11, 12	207-277 MM; 8.14-10.90 INCHES	Black	12 pairs/bag, 12 bags/carton

### For additional information visit us at [www.ansell.com](http://www.ansell.com), or call us at

#### Europe, Middle East & Africa Region

Ansell Healthcare Europe NV  
Riverside Business Park  
Blvd International, 55  
1070 Brussels, Belgium  
T: +32 (0) 2 528 74 00  
F: +32 (0) 2 528 74 01

#### North America Region

Ansell Healthcare Products LLC  
111 Wood Avenue South,  
Suite 900  
Iselin, NJ 08830, USA  
T: +1 800 800 0444  
F: +1 800 800 0445

#### Australia

Ansell Limited  
Level 3,678 Victoria Street,  
Richmond, Vic, 3121  
Australia  
T: +61 1800 337 041  
F: +61 1800 803 578

#### Asia Pacific Region

Ansell Global Trading Center  
(Malaysia) Sdn Bhd  
Prima 6, Prima Avenue  
Block 3512, Jaijan Teknokrat 6  
T: +603 8310 6688  
F: +603 8310 6699

#### Latin America & Caribbean Region

Ansell Commercial Mexico S.A. de C.V.  
Blvd. Bernardo Quintana No. 7001-C,  
Q7001 Torre II,  
Suites 1304, 1305 y 1306,  
Col. Centro Sur, c.p. 76079  
Queretaro, Qro. Mexico  
T: +52 442 248 1544 / 248 3133

#### Canada

Ansell Canada  
105 Lauder  
Cowansville, QC J2K 2K8  
Canada  
T: +1 800 363 8340  
F: +1 800 267 3551

Ansell, ® and ™ are trademarks owned by Ansell Limited or one of its affiliates. US Patented and US and non-US Patents Pending: [www.ansell.com/patentmarking](http://www.ansell.com/patentmarking) © 2024 Ansell Limited. All Rights Reserved.

Neither this document nor any other statement made herein by or on behalf of Ansell should be construed as a warranty of merchantability or that any Ansell product is fit for a particular purpose. Ansell assumes no responsibility for the suitability or adequacy of an end user's selection of gloves for a specific application.

