

Ergonomically designed to reduce hand fatigue

- **Reduced allergy risk:** MICROFLEX® XCEED® XC-310 gloves are manufactured without accelerators for low dermatitis potential. These gloves prevent instances of Type I latex allergies and Type IV chemical allergic reactions
- **Extra durability:** stronger formulation to protect against rips and tears while keeping the same tactile sensitivity
- **Enhanced comfort:** softer formulation for a lightweight, softer skin feel
- **ERGOFORM™ Technology:** MICROFLEX® XCEED® XC-310 gloves are designed with proprietary ergonomic design technology to support musculoskeletal health and increase worker productivity
- **Reduced waste:** Gloves are smartly packaged, with 250 gloves per box and easy, single glove dispensing to reduce waste
- **Strong barrier integrity:** With a low 0.65 AQL, these gloves offer advanced barrier integrity
- **Specialized protection:** These medical exam gloves are specially tested against fentanyl to ensure advanced protection and peace of mind



* see specially marked packaging

Industries

- Automotive Aftermarket
- Food Processing
- Life Sciences
- Healthcare
- Agriculture
- Emergency Medical Services
- Utilities
- Warehousing

Recommended For

- General Purpose Auto Aftermarket
- Plant disinfection and sanitization
- All food processing, applications that have food contact
- Assembly of parts
- Sample taking and processing
- Raw material sample collection
- Enhanced tactile sensitivity and dexterity, especially for delicate procedures
- Extra comfort during long, sustained procedures
- Extra comfort during long, sustained procedures
- Protection from Type IV chemical allergies in HCW's or patients
- Standard, moderate risk examination procedures

TECHNICAL DATA SHEET

Product Information	
External Glove Surface	Textured Fingers
Audit Standards	EN ISO 13485:2012
Packaging Overview	250 gloves per dispenser 10 dispensers per case 2500 gloves per case *230 gloves per dispenser (Size XL) *2300 gloves per case (Size XL)
Storage Instructions	Keep out of direct sunlight; store in a cool and dry place. Keep away from sources of ozone or ignition.
Country Of Origin	Malaysia
Product Segmentation	High Touch
Antistatic	Yes
Silicone Free	No

PHYSICAL PROPERTIES

	Typical Values		Testing Method
Length (mm/inches)	240 / 9.5		ASTM D3767,EN 420
Freedom from Holes (Inspection level I)	0.65 AQL		ASTM D5151,EN 455-1
Palm Thickness (mm/mils)	0.07 / 2.8		ASTM D3767,EN 420
Finger Thickness (mm/mils)	0.11 / 4.3		ASTM D3767,EN 420
	BEFORE AGING	AFTER AGING	
Ultimate Tensile Strength (MPa)	≥ 33	≥ 29	ASTM D412 & D573
Elongation at Break (%)	≥ 500	≥ 400	ASTM D412
Force at break (N)	≥ 7	≥ 7	EN 455-2

ORDERING INFORMATION

Size	XS (5.5 - 6)	S (6.5 - 7)	M (7.5 - 8)	L (8.5 - 9)	XL (9.5 - 10)
Product Code	XC-310-XS	XC-310-S	XC-310-M	XC-310-L	XC-310-XL

Performance Standards and Regulatory Compliance



For additional information visit us at www.ansell.com, or call us at

Europe, Middle East & Africa Region

Ansell Healthcare Europe NV
T: +32 (0) 2 528 74 00
F: +32 (0) 2 528 74 01

Asia Pacific Region

MY +603 8310 6688
apac.medical@ansell.com
CN: +86 21 38275000
infochina@ansell.com
JP: +813 5549 8151
info.medical.jp@ansell.com

North America Region

Ansell Healthcare Products LLC
T: +1 800 800 0444
F: +1 800 800 0445

Latin America & Caribbean Region

BR +55 (11) 3356-3100
latam.medical@ansell.com
MX: +52 442 296 2050
latam.medical@ansell.com
CO: +57 1 288 3247
latam.medical@ansell.com

Australia

Ansell Limited
T: +61 1800 337 041
F: +61 1800 803 578

Russia

Ansell PYC
Ten. +7 495 258 13 16

Technology



Ansell, ® and ™ are trademarks owned by Ansell Limited or one of its affiliates. US Patented and US and non-US Patents Pending; www.ansell.com/patentmarking © 2024 Ansell Limited. All Rights Reserved.

Neither this document nor any other statement made herein by or on behalf of Ansell should be construed as a warranty of merchantability or that any Ansell product is fit for a particular purpose. Ansell assumes no responsibility for the suitability or adequacy of an end user's selection of gloves for a specific application.

