

# VIKING

## WRS-D

Combined water rescue and diving suit made from a lightweight yet strong material

**Dual purpose diving suit which can be used for either surface operations or diving.**



## Industries

- Surface Rescue
- Law Enforcement
- Defense
- Fire and Rescue


## Applications

- Flooding applications
- On water rescue
- Swift water rescue

## KEY FEATURES & BENEFITS

- Lightweight durable material
- Unique "Vulca-Seam Technology" ensures watertight seams
- Abrasion and puncture resistant
- Smooth outer surface allows for easy cleaning
- Front entry, non adjustable torso, for ease of operation

## Seam Diagram



## Performance Standards



## Product Information

Product Information	
<b>Color</b>	Black legs with Yellow top
<b>Country Of Origin</b>	Lithuania
<b>Product Material</b>	Nylon outer/Butyl midply/Nylon inner.
<b>Product Reference</b>	WRS-D
<b>Reinforcements</b>	The VIKING™ WRS-D material is inherently abrasion and puncture resistant. Additional reinforcements are fitted as standard to knees and elbows. Options: Padded knees and elbows for swift water operations; buttock reinforcement panel.
<b>Seam Type</b>	Stitched and Taped
<b>Available Sizes</b>	S, M, L, XL, 2XL
<b>Standards Overview</b>	EN 14225-2:2017

## Suit Components & Accessories

Suit Components and Accessories	
<b>Design Features</b>	Front entry with non-adjustable torso. High visibility reflectors are fitted as standard to the zip flap, wrists, upper arms and back of legs.
<b>Neck Seal</b>	Fitted with a Surveor latex neck seal as standard. Options: VIKING™ Quick Neck system, which allows for rapid changing of broken seals. A silicone seal is available for those with a latex allergy.
<b>Cuffs</b>	Latex conical cuffs are the standard fitment. Options: Rubber ring system for rapid changing of cuff seals and the fitting of latex gloves. Silicone wrist seals are available for use with the rubber ring system, for those with a latex allergy.
<b>Footwear And Attachments</b>	Rubber coated 5 mm neoprene boots. The boots feature a non-slip outsole and a heel fin retainer. Other options are available.
<b>Zipper</b>	Medium Duty (MD) non-magnetic; 85 or 90 cm long; placed diagonally across the upper body. The zipper is covered by a flap.
<b>Included With Each Delivery</b>	Suspenders, carry bag, user manual, repair kit and zip care materials.

**For additional information visit us at [www.ansell.com](http://www.ansell.com), or call us at**

**Europe, Middle East & Africa Region**

Ansell Healthcare Europe NV  
T: +32 (0) 2 528 74 00

**North America Region**

Ansell Healthcare Products LLC  
T: +1 800 800 0444

**Australia**

Ansell Limited  
T: +61 1800 337 041

**Asia Pacific Region**

Ansell Global Trading Center  
T: +603 8310 6688

**Latin America & Caribbean Region**

Ansell Commercial Mexico S.A. de C.V.  
T: +52 442 248 1544 / 248 3133

Ansell, ® and ™ are trademarks owned by Ansell Limited or one of its affiliates. US Patented and US and non-US Patents Pending: [www.ansell.com/patentmarking](http://www.ansell.com/patentmarking) © 2024 Ansell Limited. All Rights Reserved.

Neither this document nor any other statement made herein by or on behalf of Ansell should be construed as a warranty of merchantability or that any Ansell product is fit for a particular purpose. Ansell assumes no responsibility for the suitability or adequacy of an end user's selection of gloves for a specific application.

